

# Digital Moisture Meter



HHMM690 moisture meter, \$95, shown smaller than actual size.

HHMM690  
**\$95**



- ✓ Measures the Moisture Content of Wood (Measurement Range of 8 to 28%)
- ✓ Simple-to-Use, One-Hand Operation
- ✓ Moisture-Indicating Lights (Green, Red, Yellow)
- ✓ Auto Power Off
- ✓ Carrying Case Included

The HHMM690 is a low-cost, simple-to-operate moisture meter for wood. Simply push the sensing pins into the wood to read the percent of moisture content (measuring range 8 to 28%).

Three lights will indicate the moisture content of the wood:

- Green:** "Air dry" condition
- Yellow:** Slightly in excess of normal
- Red:** Excess moisture

The HHMM690 works based on the principle of electrical resistance.

## Specifications

**Display:** 3-Digit LCD  
**Range:** 8 to 28% (anything above 28% is not from the wood)  
**Battery:** 4 "AAA" alkaline (included)  
**Low Battery Indication:** The "E" displays when battery is below operating level

**Accuracy:** Measurement is for estimation only;  $\pm 2\%$  between 8 and 28% moisture

**Operating Environment:** 0 to 40°C (32 to 105°F), 15 to 80% humidity

**Storage Environment:** -20 to 60°C (-4 to 140°F), 0 to 80% humidity with battery removed from meter

**Dimensions:**  
 190 H x 44 W x 40 mm D  
 (7.5 x 1.7 x 1.6")

**Weight:** Approx 5.6 oz (156 g) with battery

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description
HHMM690	\$95	Portable moisture meter

Comes with carrying case, 4 sensing pins (2 spare), 4 "AAA" alkaline batteries and manual.

**Ordering Example:** HHMM690, handheld moisture meter, \$95.

## Accessory

Model No.	Price	Description
MS-1201	\$300	Reference Book: Manufacturing Engineer's Reference Book





## UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

## CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

## GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany  
0800-8266342

## UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488

## FRANCE

[www.omega.fr](http://www.omega.fr)

Guyancourt, France  
088-466-342

## CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic  
596-311-899

## BENELUX

[www.omega.nl](http://www.omega.nl)

Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters