SCREW PLUG IMMERSION HEATERS CLEAN WATER APPLICATIONS

Starts at \$191



- ✓ 2 NPT Brass Screw Plug
- ✓ Copper Sheath Elements
- ✓ High Watt Density (61 to 67 W/in²)
- ✓ 3 to 12 kW
- Without Thermostat
- 240 and 480V, 3-Phase
- General Purpose or Moisture-Resistant/ Explosion-Resistant Terminal Enclosure

The OMEGALUX® EMT-3 Series has a copper sheath and is ideal for clean liquids within the 6 to 8 pH range.

Please Note: This immersion heater should be used with an approved temperature control device to ensure safe operation. See Section P for our selection of process controllers.

SPECIFICATIONS

Wattage: 3 to 12 kW


Power: 240 and 480 V, 3-phase Sheath: 20 cm (2") diameter copper Screw Plug: 2 NPT brass Watt Density: 61 to 67 W/in²


Enclosure:


General purpose NEMA 1 or optional type E2 moisture-resistant/explosion-

resistant enclosure.

Third-Party Approvals Enclosure: UL listed with general purpose enclosure.







MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)										
					E1 General Purpose ¹			E2 Moisture-Resistant/Explosion-Resistant ²		
kW	Phase	W/in²	No. Elem.	Dim B (in)	Model No.	Price	Wt. (lb)	Model No.	Price	Wt. (lb)
3	3	67	3	7	EMT-303/*	\$191	5	EMT-303E2/*	\$450	8
6	3	67	3	12	EMT-306/*	305	6	EMT-306E2/*	575	9
9	3	65	3	17½	EMT-309/*	430	7	EMT-309E2/*	700	10
12	3	61	3	24	EMT-312/*	575	8	EMT-312E2/*	850	11

^{*} Designate voltage: insert "240" for 240 Vac or "480" for 480 Vac.

1 Heaters with general purpose and moisture-resistant enclosures are UL Listed and CSA certified.

2 Heaters with explosion-resistant enclosures are CSA NRTL/C certified and are not intended for use in hazardous areas.

Ordering Examples: EMT-306/480, 480V, 6 kW, 3-phase general purpose heater, \$305.

EMT-312/240, 240V, 9 kW, 3-phase general purpose heater, \$575.

Your One-Stop Source for Process Measurement and Control!

One Omega Drive | Stamford, CT 06907 | 1-888-TC-OMEGA (1-888-826-6342) | info@omega.com

www.omega.com



UNITED STATES

www.omega.com 1-800-TC-OMEGA Stamford, CT.

CANADA

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

GERMANY

www.omega.de Deckenpfronn, Germany 0800-8266342

UNITED KINGDOM

www.omega.co.uk Manchester, England 0800-488-488

FRANCE

www.omega.fr Guyancourt, France 088-466-342

CZECH REPUBLIC

www.omegaeng.cz Karviná, Czech Republic 596-311-899

BENELUX

www.omega.nl Amstelveen, NL 0800-099-33-44



More than 100,000 Products Available!

Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters