

# FAST-RESPONSE THERMOCOUPLES WITH SELF-ADHESIVE BACKING

## SA1 Series

Starts at  
**\$60**  
5-pack



**177°C (350°F)  
Temperature  
Rating**



SA1-K, \$60, shown actual size.

- ✓ Special-Limits-of-Error Wire
- ✓ Self-Adhesive Backing for Easy Installation
- ✓ Better Than 0.3 Second Response Time
- ✓ 0.9 m (36") Color-Coded PFA-Insulated Leads
- ✓ Rated to 175°C (347°F) Long Term
- ✓ Available in J, K, T, and E Calibrations

OMEGA's self-adhesive thermocouples are designed for fast measurement of surface temperature. These sensors are manufactured from 30 AWG PFA-coated thermocouple wire, with a flattened bead secured between a high-temperature polymer and a high-temperature, fiber-reinforced polymer. This combination affords good thermal conductivity and fast response. The self-adhesive backing makes installation easy; no epoxy or cement is required.

### SPECIFICATIONS

#### Thermocouple Calibrations:

- J: Iron-constantan
- K: CHROME<sup>®</sup>GA-ALOMEGA<sup>®</sup>
- T: Copper-constantan
- E: CHROME<sup>®</sup>GA-constantan


**Adhesive:** Silicon-based cement

**Max Temp:** 175°C (347°F) continuous

**Min Temp:** -60°C (-75°F) continuous

**Laminates:** High-temperature polymer, fiberglass-reinforced polymer layers

**Wire:** 0.9 m (36") leads, 30 AWG PFA coated



**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order (Specify Model Number)

MODEL NO.	PRICE (PKG/5)	DESCRIPTION
SA1-(*)	\$60	Thermocouple, 36" long, stripped ends
SA1-(*)-72	80	Thermocouple, 72" long, stripped ends
SA1-(*)-SC	75	Thermocouple, 36" long, spool cap connector
SA1-(*)-72-SC	95	Thermocouple, 72" long, spool cap connector

\* Specify J, K, T or E thermocouple type. **Note:** Maximum wire length with spool cap is 72". To order probes with 120" leads, add "-120" to model number, \$100 per package of 5. **Ordering Example:** SA1-K-SC-120, package of 5 Type K thermocouples with spool caps and 120" wire leads, \$100.

#### ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CM-4363	\$85	Reference Book: Plant Design for Safety



Shown with DP25B-TC, meter, \$245, see page D-25.





#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters