

Fast Acting Fuses

MCL/MOL Fuses



Fast Acting 600V Fuse

- ✓ Compact Dimensions
- ✓ High Interrupting Rating
- ✓ Fast-Acting Design Responds Quickly to Both Overloads and Short-Circuit Current

A fast-acting, high-interrupting capacity, current-limiting type fuse. The MCL style fuse feature provides an excellent choice for applications such as: street lighting holders, HID lighting, control circuits, electronic equipment protection.

Specifications

Dimensions: 1 $\frac{1}{32}$ " ferrule, 1.5" length

Weight: Approx 0.2 lbs

Voltage Rating: MCL - 600 Vac

Ampere Rating: .1 to 50 A

Interrupting Rating:
100 K RMS amps

Agency Approvals: (0.1 to 30)
UL Listed to 198G, File E162443;
(0.1 to 30) CSA Cert. C22.2
Part 59.2, LR700489

Fast Acting 250V Fuse

- ✓ Compact Dimensions
- ✓ Economical Laminated Paper Tube Design

The MOL is an economical solution for over current protection. The MOL style fuse feature provides an excellent choice for applications such as: supplemental protection for noninductive control and lighting circuits.

Specifications

Dimensions: 1 $\frac{1}{32}$ " ferrule, 1.5" length

Weight: Approx 0.2 lbs

Voltage Rating: MOL - 250 Vac

Ampere Rating: 0.5 to 30 A

Interrupting Rating:
10 K RMS amps

Agency Approvals: (0.5 - 30)
UL Listed to 198G, File E162443;
(0.5 - 30) CSA Cert. C22.2
Part 59.2, LR700489



MCL10 shown larger than actual size.

MOL10 shown larger than actual size.

To Order

Model No.	Amp Rating	Model No.	Amp Rating
MCL.5	0.5	MCL8	8
MCL1	1	MCL10	10
MCL1.5	1.5	MCL12	12
MCL2	2	MCL15	15
MCL2.5	2.5	MCL20	20
MCL3	3	MCL25	25
MCL3.5	3.5	MCL30	30
MCL4	4	MCL35	35
MCL5	5	MCL40	40
MCL6	6	MCL50	50
Model No.	Amp Rating	Model No.	Amp Rating
MOL.5	0.5	MOL6	6
MOL1	1	MOL8	8
MOL1.5	1.5	MOL10	10
MOL2	2	MOL15	15
MOL2.5	2.5	MOL20	20
MOL3	3	MOL25	25
MOL4	4	MOL30	30
MOL5	5		

Comes with instruction sheet.

Ordering Examples: MCL10, 10 A fuse.

MOL10, 10 A fuse.