

DESK CONSOLES

NEMA 4 AND 12 OPERATOR DESK CONSOLES

SCE-DC Series



- 0.075" Thick Carbon Steel, Available in 304 and 316 Stainless Steel
- 25° Sloped Top, Hardware Installed to Prop in Open Position
- Oil and Water Resistant Gasket
- Flange Trough Collar Around All Sides of Door Opening
- Removable Doors with Concealed Hinge and Removable Print Pocket
- Ground Studs on Door and Body
- Rubber Pads with Provision for Leveling Pads on Bottom of Enclosure
- Black, Quarter Turn Latches on Top Door
- Key Locking Black 3-Point Flush Swing-Handles on Door
- Mounting Studs and Channels Welded on Sides of Interior Body for Mounting Additional Panels on Dual Access Console
- Mounting Hardware Included with Each Additional Sub-Panel



SCE-402516SDC, single access single door desk console. Shown smaller than actual size.

The SCE-DC Series of desk consoles are intended for indoor use to house electronic and electrical instruments and controls. These operator control panels will protect electrical components against introduction of solid foreign objects, falling dirt and water. These units can be used in a standing or sitting position and can allow for installation of operator interface, control pushbuttons and selector switches.

Models are available with one or two door access in both the front and rear of the enclosure. Sub-panels are available for mounting electrical components and dual access models come with channels for more than one sub-panel installation.

SPECIFICATIONS

Finish: ANSI-61 gray powder coating inside and out. Optional sub-panels are powder coated white.

Industry Standards (IS2):

NEMA: Type 4, 12 and Type 13

UL Listed: Type 4 and 12

CSA: Type 4 and 12

IEC: 60529 IP 66

Industry Standards (IS1):

NEMA: Type 12 and Type 13

UL Listed: Type 12

CSA: Type 12

IEC: 60529 IP 55

**For HMI's,
Power Supplies
and Terminal
Blocks Visit us
Online!**



SCE-402516SDC, single access single door desk console. Shown smaller than actual size.



SCE-464919SDC, single access two door desk console shown being used in an engine test bay.

To Order

MODEL NO.	HEIGHT (inch)	WIDTH (inch)	DEPTH (inch)	INDUSTRY STD RATING	WEIGHT lbs	SUB-PANEL	HEIGHT (inch)	WIDTH (inch)
SINGLE ACCESS SINGLE DOOR								
SCE-402516SDC	40.25	25.25	15.5	IS2	147	SCE-30P24	27	21
SCE-403716SDC	40.25	37.25	15.5	IS1	167	SCE-36P30	33	27
SCE-462519SDC	46.25	25.25	18.5	IS2	172	SCE-36P24	33	21
SCE-463719SDC	46.25	37.25	18.5	IS1	200	SCE-36P36	33	33
DUAL ACCESS SINGLE DOOR								
SCE-462519DC	46.25	25.25	18.5	IS2	140	SCE-36P24	33	21
SCE-463719DC	46.25	37.25	18.5	IS1	192	SCE-36P36	33	33
SINGLE ACCESS TWO DOOR								
SCE-464919SDC	46.25	49.25	18.5	IS1	225	SCE-48P36	45	33
SCE-466019SDC	46.25	59.88	18.5	IS1	250	SCE-60PC36	55.63	33
DUAL ACCESS OVERLAPPING TWO DOOR								
SCE-464919DC	46.25	49.25	18.5	IS1	215	SCE-48P36	45	33
SCE-466019DC	46.25	59.88	18.5	IS1	240	SCE-60PC36	55.63	33
DUAL ACCESS TWO DOOR WITH CENTER CHANNEL								
SCE-464919DCC	46.25	49.25	18.5	IS2	235	SCE-48P36	45	33
SCE-466019DCC	46.25	59.88	18.5	IS2	255	SCE-60PC36	55.63	33

Ordering Examples: SCE-402516SDC, single access single door desk console, 40.25 H x 25.25 W x 15.50" D and SCE-30P24 sub-panel. SCE-464919SDC, single access two door desk console, 46.25 H x 49.25 W x 18.5" D and SCE-48P36 sub-panel.