

OMEGAPHONE® Automatic Temperature Alarm Dialer

OMA-VM500-3



- ✓ Monitors Temperature and Power Status
- ✓ Programmable High and Low Limits for Temperature
- ✓ Program up to Four 20 Digit Phone Numbers
- ✓ Works with Telephone Pagers
- ✓ Easy-to-Follow Menu Driven Programming Done Over the Phone

The OMA-VM500-3 is a full-featured monitor and alarm system that monitors temperature and power status wherever the unit is located. This system can dial up to four phone numbers, and the integrated voice tells you the temperature and whether the power is on or how long the power has been off. You can also call the unit at anytime and hear a status report that gives you an update on the conditions at your facility.

The OMA-VM500-3 is easily programmed over the phone. Simply locate the unit in the area where you want to measure the temperature. Plug in the phone line and the power adapter and turn the unit on. Call the unit from another phone or cell phone and follow the spoken instructions to program the temperature limits and the emergency phone numbers. The system is now programmed and is monitoring temperature and power at your facility.

Specifications

Temperature Measurement

Range: 32 to 125°F (0 to 52°C); unit is set up factory default for Fahrenheit operation (can be changed in the field for Celsius operation)

Temperature Sensor: Solid state

Accuracy: 2°F

High and Low Programmable

Temperature Limits: 35 to 125°F



OMA-VM500-3, shown smaller than actual size.

Operating Ambient:

0 to 52°C (32 to 125°F)

Telephone: Standard RJ11 phone jack connection

Telephone Numbers: Stores up to four phone numbers up to 20 digits long

Personal Identification Message: Record up to a 10-second message over the phone

Operation: With answering machine on the same phone line

Power: From included 120 Vac wall mount transformer power supply

Battery Backup: 4 hour rechargeable battery backup; 30 hours optional

Dimensions:

140 H x 127 W x 64 mm D (5.5 x 5 x 2.5")

Material: ABS plastic

Weight: 0.45 kg (1 lb)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order Visit omega.com/oma-vm500-3 for Pricing and Details

Model Number	Description
OMA-VM500-3	Automatic temperature alarm dialer
OMA-VM500-3-B30	Temperature alarm dialer with 30-hour battery backup

Comes complete with 120 Vac power supply and operator's manual.

Ordering Example: OMA-VM500-3-B30 automatic temperature alarm dialer with 30-hour battery backup and OCVW-1 OMEGACARESM 1-year extended warranty adds 1 year to standard 1-year warranty.