

OMEGAPHONE® 7-Channel, 4 to 20 mA Input Alarm Dialer Model OMA-VM500-4

Starts at
\$615



OMA-VM500-4, \$615, shown smaller than actual size.

- ✓ Monitors 7-Channels of 4 to 20 mA Input, One Dry-Contact Input, and Power Status
- ✓ Isolated Inputs Prevent Ground Loops
- ✓ Program Up to Four 20-Digit Phone Numbers
- ✓ Works with Telephone Pagers
- ✓ Integral 4-Line LCD
- ✓ Wall-Mount Enclosure

Model OMA-VM500-4 monitors up to seven 4 to 20 mA inputs and dials up to 4 phone or pager numbers if any 4 to 20 mA input goes out of limits, if the dry-contact input is not in its programmed normal state, or if there is a power outage. The integrated voice tells the user which input is out of limits. The user can call the unit at any time to hear a report on the input and power status.

The OMA-VM500-4 is easily programmed over the phone. Simply locate the unit in the area where you want to measure the 4 to 20 mA inputs, plug in the phone line and the power adaptor, turn the unit on, and call the unit from another phone or cell phone. Follow the spoken instructions and the instructions in the operator's manual to program the phone numbers where you want the dialer to call in case of an alert condition and the upper and lower limits for the 4 to 20 mA signals. Then hang up by pressing the "0" key on your phone until the unit says "good-bye." The system is now programmed and is monitoring your facility for 4 to 20 mA input and power status.

Specifications
Number of Analog Inputs: 7
Sensor Type: Self-powered 4 to 20 mA output sensors




Sensor Input: Isolated, 20 Ω input impedance
Response Time: 50 ms
Accuracy: ± 0.05 mA
High and Low Limits on 4 to 20 mA Inputs: Programmable
Scaling in Engineering Units for Each 4 to 20 mA Input: Programmable
Dry-Contact Input: 12 Vdc 10 mA source; input is normally open
Telephone: Standard RJ11 phone jack connection
Telephone Numbers: Stores up to 4 phone numbers up to 20 digits long
Personal Identification Message: Records up to a 10-second message over the phone
Operation: Operates with answering machine on the same phone line
Display: Integral 4-line LCD
Alarm Notification: Alarm siren sounds and alarm relay closes if any input goes out of limits
Alarm Cancellation: Pushbutton on front of the unit silences the alarm and cancels emergency telephone calls

Alarm Relay Output: 5 A, 125 Vac
Alarm Buzzer: 85 dB
Power: Powered from included 120 Vac wall mount transformer power supply
Battery Backup: 4-hour rechargeable battery backup; 20 or 30 hours optional
Operating Temperature: 0 to 52°C (32 to 125°F)
Electrical Connections: Plug-in terminal block
Dimensions: 117 H x 223 W x 57 mm D (4.62 x 8.79 x 2.26")
Material: ABS plastic
Weight: 0.9 kg (2 lb)

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)		
Model Number	Price	Description
OMA-VM500-4	\$615	7-channel automatic 4 to 20 mA input alarm dialer with integral LCD
OMA-VM500-4-B20	652	7-channel automatic 4 to 20 mA input alarm dialer with 20-hour battery backup and integral LCD
OMA-VM500-4-B30	681	7-channel automatic 4 to 20 mA input alarm dialer with 30-hour battery backup and integral LCD
CS-3791	150	Reference Book: Standard Handbook of Electronics Engineering 

Each unit comes with complete operator's manual.
Ordering Example: OMA-VM500-4-B20, 7-channel automatic 4 to 20 mA alarm dialer with 20-hour battery backup and integral LCD display, OMEGACARESM, 1-year extended warranty for OMA-VM500-4-B20 (adds 1 year to standard 1-year warranty), \$652 + 65 = \$717.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters