

# OMB-DBK1

## 16-Connector BNC Interface Module for OMB-DAQBOARD-2000 Series and OMB-LOGBOOK



Model OMB-DBK1

# \$419



The OMB-DBK1, \$419, shown smaller than actual size, provides sixteen channels of analog input via BNC connectors

- ✓ Provides Access to 16 Analog Inputs Via BNC Connectors
- ✓ Features Per-Channel 100K Ohm Bias Resistors for Differential Inputs

The OMB-DBK1 provides a convenient means of attaching analog signals from BNC cables to the OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems.

Its 16 BNC connectors accommodate 16 single-ended inputs or 8 differential analog inputs.

Each differential input is equipped with a switchable 100K Ohm bias resistor referenced to analog common. The unit also provides a ground reference via an external ground connection.

The OMB-DBK1 features a male DB37 connector that mates with the OMB-LOGBOOK and OMB-DAQBOARD-2000 Series.

### Signal Termination

Since the OMB-DBK1 is a passive universal interface, it also provides a convenient method of connecting analog signals to other I/O devices. The unit's 16 easy-to-access BNC connectors can be configured as differential or single-ended.

### Specifications

#### Connector:

DB37 male, mates with P1 pinout on the OMB-LOGBOOK and OMB-DAQBOARD-2000 Series BNC connectors for signal inputs

#### Analog Input Connection:

One BNC connector for each of 16 analog input channels

#### Dimensions:

221 W x 285 L x 35 mm H (8.5 x 11 x 1.375")

**Weight:** 1.3 kg (3 lbs)

#### Cables:

Use OMB-CA-37-x with OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model Number	Price	Description
OMB-DBK1	\$419	16-connector BNC Interface

Ordering Example: OMB-DBK1 16-connector BNC interface module, \$419.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters