


OMB-DBK8

8-Channel High-Voltage Input Card for OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

Model OMB-DBK8

\$749



- ✓ Provides 8 High-Voltage Input Channels
- ✓ Per-Channel Selection of Three Voltage Ranges Via Jumper
- ✓ Provides 10 MΩ Input Impedance for Minimum Loading Errors
- ✓ Buffered Inputs on Each Channel for High-Speed Scanning

The 8-channel OMB-DBK8 high-voltage input card provides 3 input ranges, which can be set on a per-channel basis

Each of the OMB-DBK8's inputs provides an individual buffer amplifier that allows the combination of high-speed (10 μs/reading) and high-input impedances.

As many as thirty-two OMB-DBK8 cards can be used in one system, for a total of 256 high-voltage differential inputs.

Specifications

Connector: DB37 male, mates with P1 pinout on the OMB-LOGBOOK or OMB-DAQBOARD-2000; screw terminals for signal inputs

Voltage Input Ranges: ±10 Vdc, ±50 Vdc, ±100 Vdc; selection by jumper for each channel

Input Impedance: 10 MΩ

Attenuation:

10 V	$V_{out} = V_{in}/2$
50 V	$V_{out} = V_{in}/10$
100 V	$V_{out} = V_{in}/20$

Bandwidth: 15 kHz

Attenuation Accuracy: 0.5%

Offset Voltage

Typ: 0.5 mV
Max: 2.0 mV

Offset Drift

Typ: 4 μV/°C
Max: 10 μV/°C

Cables:

Use OMB-CA-37-x with OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

The OMB-DBK8 provides eight high-impedance, high-voltage input channels for OMEGA's OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems. The OMB-DBK8 accommodates 10, 50, or 100 VFS bipolar inputs that you can set on a per-channel basis via jumpers on the card.

The OMB-DBK8's 10 MΩ input impedance presents minimal loading of high impedance circuits and transducers (*e.g.*, string pots), which ensures accurate readings over a wide range of source impedance, and high impedance transducers, such as string pots.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
OMB-DBK8	\$749	8-Channel High-Voltage Input Card

Ordering Example: OMB-DBK8 8-channel high-voltage input card, \$749.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters