

Dual Channel High Speed Serial Interface

Synch/Async RS-530/422/485 Operation




OMG-ACB-530
\$299
 Basic Unit



- ✓ 85230 Serial Communications Controller
- ✓ DMA Supports Data Rates Greater than 1 Million BPS
- ✓ Full Duplex DMA Transfer Capability on Both Channels A and B
- ✓ Selectable Port Address, IRQ Level (2, 3, 4, 5, 7, 10-12, 15) and DMA Channels (0, 1, 2, 3)
- ✓ DMA Terminal Count Interrupt Supported
- ✓ OEM Security Feature for Software Protection
- ✓ WIN 95/98/Me/NT/2000 HDLC/SDLC Drivers, Applications and Sample Source Code Included

Applications

- ✓ Users Requiring Protocols such as SDLC, HDLC, X.25, MONOSYNC, BISYNC, and ASYNC
- ✓ Fractional T1 Pipelines/Data Highways
- ✓ PLC Communications
- ✓ Flexibility of Board Design Allows Interfacing with a Variety of Standard and Unusual Protocols



Shown smaller than actual size.

The OMEGA® Advanced Communications Boards (ACBs) allow the user to configure a high speed, low cost SYNC/ASYNCR communications solution. Protocols supported include X.25, SDLC, HDLC, MONOSYNC, BISYNC, and high speed ASYNC. The serial Communications Controller allows Full Duplex communications at speeds greater than 1M bps without the added cost of an intelligent communications coprocessor. This feature gives the ACB user an unparalleled cost/performance ratio. Models are available with one or two communication ports and support for a variety of communication standards. Both ports can be operated in full duplex DMA mode. Using this feature, both channels can operate at very high data rates with DMA.

Specifications

Controller: 85230-8

Ports:

OMG-ACB-503-I: single port

RS-530, RS-422 or RS-485

OMG-ACB-530-II: dual port

RS-530, RS-422 or RS-485

Max Data Rate: 1.8432M bps

Max Data Distance: 5000 ft at

9600 bps

RS-485 Operation: two or four-wire

Operating Ambient: 0 to 50°C

(32 to 122°F), 0 to 90% RH

Storage Ambient: -20 to 70°C

(-4 to 158°F)

Power: +5 V @ 195 mA

Connector(s): DB25P;

EIA-530-DTE

To Order (Specify Model Number)

Model Number	Price	Description
OMG-ACB-530-I	\$299	Single port RS-530/422/485 interface
OMG-ACB-530-II	319	Dual port RS-530/422/485 interface
OMG-ACB-530-CAB-01	25	RS-449 cable adaptor converts RS530 pinout to RS-449 male, 9"

Each unit supplied complete with operator's manual and software tool kit

Ordering Example: OMG-ACB-530-II dual RS-530/422/485 interface and OMEGACARESM 1-year extended warranty (adds 1 year to standard 1-year warranty), \$319 + 31 = \$350.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters