

Four Port ISA RS232 Interface

OMG-VERSACOMM4-EX



- ✓ Four Port RS232 Interface
- ✓ Each Port Designed to Maximize Windows XP/Vista/7 Communications
- ✓ 16554 Buffered UART std/ Full Array of Advanced UARTS Available
- ✓ Supports Standard PC Data Rates and “Quad” Data Rates up to 460.8 Kbps
- ✓ Flexible Address Selection Via Dip-Switch
- ✓ Ten Interrupt Selections Including (3–7, 9–12, and 15)
- ✓ Interrupts Can be Shared or Individually Selected Per Port to Simplify Installation
- ✓ Onboard Interrupt Status Port Provides Efficient Interrupt Sharing
- ✓ Compatible with Windows XP/Vista/7 and Other Operating Systems
- ✓ Includes Windows Advanced COM Drivers and Help Files to Simplify Installation

The OMG-VERSACOMM4-EX provides the PC with four RS232 Async links to data collection equipment and other devices.

This product features extended interrupt support, individually selectable or sharable interrupts, and an onboard interrupt status port for maximum Windows flexibility. Windows XP/Vista/7 drivers are included. The drivers provide IRQ sharing, advanced UART support and serial diagnostic utilities.



OMG-VERSACOMM4-EX, shown smaller than actual size.

Specifications

Communications Chip: 16554 UART

Number of Ports: Four RS232

Max. Data Rate: 460.8 Kbps

Max. Data Distance: up to 15.2 (50')

Operating Temperature: 0 to 50°C (0 to 122°F)

Storage Temperature: -20 to 70°C (-4 to 158°F)

Humidity Range: 10 to 90% RH

Current Specifications: +5V @ 210 mA, ±12V @ 80 mA ea.

Connector(s): DB-37 to (4) DB-25P or DB-37 to (4) DB-9P

Cable Length: 91.44 cm (36")

Dimensions: 5.2 L x 3.4" H (13.21 x 8.64 cm)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order

Model Number	Description
OMG-VERSACOMM4-EX-DB25	Four port RS232 interface (DB-25 cable included)
OMG-VERSACOMM4-EX-DB9	Four port RS232 interface (DB-9 cable included)

Comes complete with coperator's manual and serial utility disk.

To order with optional 16654 UART, add suffix “-SS” to part number and additional cost to price.

Ordering Example: OMG-VERSACOMM4-EX-DB25-SS, four port RS232 interface with DB-25 cable and 16654 UART upgrade, and OCW-1 OMEGACARESM 1 year extended warranty (adds 1 year to standard 1 year warranty).