

## **Mini Vacuum Desiccator** *Ideal for Small Samples*

**LAB-410990000**

**Product Discontinued**

- Interior Volume: 0.015 Cu. Ft.
- Vacuum Rating of 740 mm Hg (29")
- Clear Polycarbonate Top; White Polypropylene Bottom
- Stopcock with 2 mm (0.08") PTFE Plug  
Uses 6 mm (¼") Tubing
- Peripheral Flange Around the Bottom Fits Into Two Snap  
Locks and Seals the Two Halves Against a Buna-O-Ring



LAB-410990000 shown smaller than actual size.

### To Order

| Model No.     | Description            | Dimensions (Diameter x H) |
|---------------|------------------------|---------------------------|
| LAB-410990000 | Mini vacuum desiccator | 17.5 x 12.6 cm (6¾ x 5")  |