

# LEVEL ALERT SINGLE SENSOR CONTROLLER (DC)

LVCN-8  
\$210



LVCN-8, \$210, shown smaller than actual size.



- ✓ Calls Immediate Attention to Alarm Conditions
- ✓ High Intensity Strobe Light Reduces Operator Error
- ✓ Convenient Reminder to Refill Tank
- ✓ Mounts Directly on Sensor or Adjustable Track System
- ✓ Time Delay Relay
- ✓ Controls, Pumps, Valves, Alarms
- ✓ Swivels On Base for Easy Conduit Alignment



OMEGA's DC level alert calls immediate attention to alarm conditions. For operator alert to low inventory levels or high alarm conditions, the level alert offers an excellent solution to these problems. An amber lens distributes the high intensity strobe light in a pattern which calls immediate attention to alarms. The visual alert combined with a controller makes it both a cost effective and easy to install device. The controller can be mounted on a sensor or the OMEGA® track system.

## SPECIFICATIONS

**Voltage Input:** 14 to 36 Vdc

**Max Current Consumption:** 0.25 amps

**Lighting Element:** High intensity lamp

**Brightness:** Greater than 50,000 CP

**Relay Output:** Isolated and sealed single pole double throw (SPDT) relay, Form C

**Switching Mode:** Selectable, NO or NC states

## Relay Switching Voltage:

14 to 36 Vdc

**Max. Switched Current:** 6 amps

**Time Delay:** Adjustable from 0.15 to 60 seconds

## Temperature Range:

-40 to 70°C (-40 to 158°F)

**Sensor Volt Supply:** Nominal 13.5 Vdc @ 100 mA

**Sensor Trigger Pt.:** Dry <12 mA or wet >12 mA

**Mounting Connection:** 3/4" NPT

**Conduit Connection:** 1/2" NPT

**Enclosure Material:** Polypropylene (PP), flame retardant

**Enclosure Rating:** NEMA 4X (IP65)

**Dimensions:** 7.1 Dia. x 13.97 cm H (2.8 x 5.5") x 3/4" NPT

## Flash Alarm:

**Flash Type:** Xenon tube

**Flash Frequency:** 1 per second

**Strobe Life:** 10M cycles

**Material:** Polycarbonate

**Color:** Amber

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description	Material	Size
LVCN-8	\$210	Level alert single sensor controller	PP	2.8 x 5.5 x 3/4" NPT

Comes with complete operator's manual.

**Ordering Example:** LVCN-8, single sensor controller, \$210.

## Accessory

Model No.	Price	Description
ES-2247	\$125	Reference Book: The Consumer Guide To Differential Pressure Flow Transmitters



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters