

# BATTERY POWERED LEVEL TRANSMITTER AND DISPLAY



LVU-19  
**\$895**



- ✓ Accurate and Reliable Level Measurement from 15 cm to 3.7 m (6" to 12')
- ✓ Low-Cost Solution for OEM and Process Applications
- ✓ Compact Size and 5.1 mm (2") Transducer for Small and Medium Size Tanks
- ✓ Transmitter Features PP Enclosure Rated NEMA 4X with PVDF Transducer
- ✓ Display Features Polycarbonate Enclosure Rated NEMA 4X with Clear Faceplate
- ✓ Large 3.5 Digit 8.9 cm (0.5") LCD with Floating Decimal Point
- ✓ Engineering Units on Display Range from -500 to 1999
- ✓ Simple Potentiometer Calibration for all Display Set Points

A high frequency ultrasonic sound wave is pulsed three times per second from the base of the transducer. The sound wave reflects against the process medium below and returns to the transducer. The microprocessor based electronics measure the time of flight between the sound generation and receipt, and translates this figure into the distance between the transmitter and process medium below.

The LVU-19 features two portions, a level transmitter and a compact display, that are both rated NEMA 4X. The level transmitter is mounted through the top wall of the tank and provides non-contact measurement up to 3.7 m (12'). The display is mounted to the side of the tank and provides local indication. The entire system is powered via a 18 Vdc battery supply and can be activated by a moment switch located below the display. With non-contact technology, the transmitter and display are an excellent choice for applications with dirty, coating, corrosive type liquids. The compact design is the perfect size for small and medium tank applications.



LVU-19, \$895, shown smaller than actual size.



## SPECIFICATIONS

**Range:** 15.2 cm to 3.7 m (0.5 to 12')  
**Accuracy:** ±0.25% of span in air  
**Resolution:** 3 mm (0.125")  
**Frequency:** 50 kHz  
**Pulse Rate:** 3 per second  
**Beam Width:** 8° conical  
**Dead Band:** 15.2 cm (0.5") min. standard conditions  
**Supply Voltage:** 18 Vdc  
**Battery Supply:** 2 x 9 Vdc batteries (included)  
**Loop Resistance:** 300 ohms @ 18 Vdc  
**Signal Interface:** 4 to 20 mA  
**Fail-safe Diag.:** Reverts to 22 mA  
**Display Type:** LCD, 3.5 digits  
**Display Size:** 8.9 cm (0.5")  
**Calibration Adj.:** Dual potentiometers  
**LED Indication:** Power & Fail Safe  
**Temp. Rating:** -40 to 60°C (-40 to 140°F)  
**Temp. Comp.:** Over entire range  
**Pressure Rating:** 30 psi (2 bar) @ 25°C, derated @ 1.667 psi (0.113 bar) per °C above 25°C  
**Enclosure Rating:** NEMA 4X (IP65)  
**Trans. Material:** Encl: PP (U.L. 94 VO) Transducer: PVDF  
**Display Material:** Polycarbonate  
**Mounting Threads:** 2" NPT (2" G)  
**Conduit Conn.:** ½" NPT  
**Cable Length:** 4.5 m (15')

**Mounting Gasket:** Viton® (2") metric only

**Overall Dimensions:**  
 71 W x 137 mm L (2.8 x 5.4")

**Display Dimensions:**  
 140 W x 80 H x 65 mm D  
 (5.51 x 3.15 x 2.5")

## APPLICATION VARIABLES

	Variable	Yes	No
Liquid	General Purpose	✓	
	Conductive	✓	
	Non-conductive	✓	
	■ Conductivity	✓	
	Contact		✓
	Non-contact	✓	
	Clean	✓	
	Dirty	✓	
	Coating	✓	
	Non-coating	✓	
	Vapors		✓
	■ Gas Density		✓
	Vacuum		✓
	Ambient pressure	✓	
	Low Pressure	✓	
	Medium Pressure		✓
Intrinsically Safe		✓	
Integral Relay		✓	
Foam		✓	

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)		
Model No.	Price	Description
<b>LVU-19</b>	<b>\$895</b>	Battery powered level transmitter and display, 2" NPT
<b>LVU-19-G</b>	<b>900</b>	Battery powered level transmitter and display, 2" G thread
<b>GE-2427</b>	<b>105</b>	Ultrasound and Elastic Waves

Comes with complete operator's manual.

**Ordering Example:** LVU-19, Battery powered level transmitter and display with a 2" NPT thread, \$895.





#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters