



pH Meter and Calibration Kits Digital Handheld pH Meters Model PHH-45D

PHH-45D



- ✓ Rugged Case is Acid and Solvent Resistant
- ✓ Extremely Cost-Effective
- ✓ Easy to Use
- ✓ Dual Point Calibration

The PHH-45D pH meter is a cost-effective unit with a taut band meter movement in a sturdy solvent-and-acid-resistant housing. It is a full function solid state instrument capable of measuring pH from 0 to 14 with the aid of offset ranging. The unit features manual temperature compensation from 0 to 100°C (32 to 212°F) and dual point calibration. Attractive and durable, the meter comes packaged in a kit with a gel-filled combination pH electrode, three buffers (pH 4, 7, 10), battery, and a foam-lined carrying case. This inexpensive but reliable pH meter is simple to use and is perfect for use in the field, laboratory, or plant.

Specifications

- Range:** pH 2 to 12 (0 to 14 with offset ranging)
- Readability:** 0.1 pH
- Accuracy:** ±0.1 pH
- Precision:** ±0.1 pH
- Temperature Compensation:** Manual, 0 to 100°C (32 to 212°F)
- Connector:** BNC
- Battery:** 9 V (included)



Each unit comes complete with meter, combination electrode, 4, 7, 10 buffer solution, carrying case, screwdriver, battery and operator's manual.



PHH-45D
Shown actual size.

DISCONTINUED

To Order	
Model No.	Description
PHH-45D	Handheld pH meter

Accessories

Model No.	Description
PHE-1304	Replacement electrode
PHA-4	Buffer solution, pH 4.00
PHA-7	Buffer solution, pH 7.00
PHA-10	Buffer solution, pH 10.00

Each unit is supplied complete with meter, combination electrode, 4, 7, 10 buffer solutions, carrying case, battery and complete operator's manual.

Ordering Examples: PHH-45D, pH meter and PHE-1304, replacement electrode.

PHH-45D, pH meter and PHA-4, 4.0 pH 4 buffer, PHA-7, 7.0 pH 7 buffer.