

Stirrer Hot Plates

STR-11 Series



Product Discontinued

as of November 2017



These OMEGA® general purpose stirrers are a cost efficient and worry free solution for any lab.

Our stirrers offer a soft start stir control which helps prevent stir bar disengagement and possible disruption to the solution even when the stir control is turned to maximum quickly. Sophisticated safety features: Ceramic microcrystal plate, which are more chemical, high temperature and acid resistant, the spill prevention system outer case design.

STR-11 shown smaller than actual size.

SPECIFICATIONS

Plate Dimensions, mm (inch)

STR-11: 160 x 160 (6.3 x 6.3)

STR-12: 300 x 300 (11.8 x 11.8)

Heated Area Dimensions, mm (inch)

STR-11: 120 x 120 (4.72 x 4.72)

STR-12: 220 x 220 (8.66 x 8.66)

Heated Power

STR-11: 550 W

STR-12: 1800 W

Maximum Plate Temperature

STR-11: 550°C (1022°F)

STR-12: 550°C (1022°F)

Stirrer Speed (rpm): 100 to 1500

Stirring Capacity, Maximum (Liters): 20

Dimensions, mm (inch)

STR-11: 220 W x 240 L x 145 D (8.66 x 9.44 x 5.7)

STR-12: 330 W x 380 L x 145 D (13 x 14.9 x 5.7)

Net Weight, kg (lb)

STR-11: 3.6 (7.9)

STR-12: 8.5 (18.7)

Power Supply: 120V, 60 Hz

To Order	
Model No.	Description
STR-11	Ceramic top stirrer
STR-11H	Microcrystal top stirrer hot plate
STR-12	Ceramic top stirrer
STR-12H	Microcrystal top stirrer hot plate

All units are supplied with stir bar and mains lead.