


SCREW PLUG IMMERSION HEATERS FOR SMALL TANKS

RI, RIO, RIS Series



- ✓ Stocked for Fast Delivery
- ✓ 1/2 and 3/4 NPT
- ✓ Cartridge Type Element
- ✓ Premium Quality
- ✓ Rugged Construction



Type RI with Incoloy Sheath—Brass Pipe Thread

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)									
Watts	Phase	W/in ²	Dimensions: cm (in)			Std. Pipe Thd.	Model No.	Price	Wt. kg (lb)
			A	B	C				
100	1	31	12 (4 7/8)	4 (1 1/2)	1.6 (5/8)	1/2	RI-100/120V	\$150	1 (3)
250	1	33	17 (6 5/8)	9 (3 1/2)	1.6 (5/8)	1/2	RI-250/(*)	157	2 (4)
500	1	34	30 (11 5/8)	16 (7 7/8)	1.6 (5/8)	1/2	RI-500/(*)	165	5 (10)
750	1	33	40 (15 3/8)	30 (12)	1.6 (5/8)	1/2	RI-750/(*)	177	6 (14)
300	1	30	21 (8 1/8)	12 (4 1/16)	1.6 (5/8)	3/4	RI-1300/(*)	164	4 (8)
500	1	36	26 (10 1/4)	16 (6 3/16)	1.9 (3/4)	3/4	RI-1500/(*)	177	4 (9)
750	1	32	37 (14 3/8)	27 (10 5/16)	1.9 (3/4)	3/4	RI-1750/(*)	188	6 (13)
1000	1	32	37 (14 3/8)	34 (13 3/8)	1.9 (3/4)	3/4	RI-1100/(*)	200	7 (15)

These screw plug immersion heaters feature a dead front nylon twist-lock grounded plug with receptacle. Cord is supplied by the user. The cartridge element is brazed to a standard 1/2" or 3/4" screw plug.

SPECIFICATIONS

Power: 100 to 1000 watts

Voltage: 120 or 240 Vac, 1 phase

Watt Density: 20 to 36 W/in²

Sheath: Type RI has a 1.6 cm (5/8") or 1.9 cm (3/4") Incoloy sheath; Type RIO has a 1.6 cm (5/8") or 1.9 cm (3/4") diameter stainless steel sheath; Type RIS has a 1.6 cm (5/8") diameter passivated stainless steel sheath

Screw Plug:

Type RI has 1/2" or 3/4" NPT brass screw plug; Type RIO has 1/2" or 3/4" NPT steel screw plug; Type RIS has 1/2" NPT passivated stainless steel screw plug

Type RIO with SS Sheath—Steel Pipe Thread

Watts	Phase	W/in ²	Dimensions: cm (in)			Std. Pipe Thd.	Model No.	Price	Wt. kg (lb)
			A	B	C				
150	1	20	17 (6 5/8)	9 (3 1/2)	1.6 (5/8)	1/2	RIO-150/120V	\$157	2 (4)
300	1	20	28 (10 9/16)	16 (7 7/8)	1.6 (5/8)	1/2	RIO-300/(*)	165	5 (10)
500	1	22	39 (15 1/16)	30 (12)	1.6 (5/8)	1/2	RIO-500/(*)	177	6 (14)
200	1	20	21 (8 1/8)	12 (4 1/16)	1.9 (3/4)	3/4	RIO-1200/(*)	164	4 (8)
300	1	22	26 (10 1/8)	16 (6 3/16)	1.9 (3/4)	3/4	RIO-1300/(*)	177	4 (9)
500	1	21	37 (14 3/8)	27 (10 5/16)	1.9 (3/4)	3/4	RIO-1500/(*)	188	6 (13)
600	1	20	44 (17 3/8)	34 (13 3/8)	1.9 (3/4)	3/4	RIO-1600/(*)	206	7 (15)

Type RIS with Passivated SS Sheath and Screw Plug

Watts	Phase	W/in ²	Dimensions - cm (in.)			Std. Pipe Thd.	Model No.	Price	Wt. kg (lb)
			A	B	C				
250	1	35	17 (6 5/8)	9 (3 1/2)	1.6 (5/8)	1/2	RIS-255/120V	\$385	3 (6)
500	1	28	28 (10 9/16)	20 (7 7/8)	1.6 (5/8)	1/2	RIS-505/120V	430	5 (10)
750	1	31	38 (15 1/8)	30 (12)	1.6 (5/8)	1/2	RIS-755/120V	460	7 (15)

(*) To specify voltage, insert "/120V" for 120 Vac or "/240V" for 240 Vac.

Ordering Examples: RIO-500/240, 500 W heater, 1.6 cm (5/8") dia. stainless steel sheath and 1/2" NPT steel screw plug powered by 240 Vac, \$177.

RIS-255/120V, 250 W heater, 1.6 cm (5/8") dia. passivated stainless steel sheath and 1/2" NPT steel screw plug powered by 120 Vac, \$385.

CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters