

WRAP-AROUND TOTE TANK HEATERS

TOTE Series



- ✓ Fits Any Tote Tank from 1 to 1.2 m (40 to 48") Square
- ✓ Comes in Heights of 0.9, 1.1 or 1.2 m (36, 42 or 48")
- ✓ 2 Heating Zones
- ✓ 2 Built-In Adjustable Thermostats
- ✓ 2 Built-In High-Limit Thermostats
- ✓ Adjustable Nylon Straps with Buckles
- ✓ Flexible Silicone-Impregnated Cloth Facing and Liner
- ✓ 6 mm (¼") Fiberglass Insulation
- ✓ 1.8 m (6') Power Cord

The OMEGA® TOTE Series tank heaters are flexible wrap-around surface heaters offered in different sizes based on height. These heaters provide a quick, easy, non-invasive way to warm your product. They fit nearly every standard tote tank utilizing adjustable nylon straps with buckles. There are 3 straps for placing around the tank and 2 for across the top. Units include an adjustable thermostat and a manual reset high-limit thermostat for each of the 2 zones.

SPECIFICATIONS

Adjustable Thermostat Setting: 10 to 70°C (50 to 160°F)

High-Limit Thermostat Setting: Approximately 90°C (195°F)

High-Limit Thermostat Reset: Manual



TOTE481-ADJ/120V shown smaller than actual size.

Maximum Exposure Temperature: 230°C (450°F)

Outer Sheath and Liner: Silicone impregnated

Attachment Method: Nylon straps with adjustable buckles

Fiberglass Insulation: 6 mm (0.25")

Total Blanket Length: Approximately 5 m (16.5')

Heated Length: Approx 4.1 m (13.5')

Height: 0.9 m (36"), 1.1 m (42") or 1.2 m (48")

Wattage: 1440 or 2880 W

Power Cord: 1.8 m (6') with standard power plug

Power: 120 or 240 Vac

To Order

| Model No. | Description | Weight |
|------------------|---|---------------|
| TOTE361-ADJ/120V | Tote heater with thermostat, 120V, 1440 W, 0.9 m (36") height | 18 kg (40 lb) |
| TOTE362-ADJ/240V | Tote heater with thermostat, 240V, 2880 W, 0.9 m (36") height | 18 kg (40 lb) |
| TOTE421-ADJ/120V | Tote heater with thermostat, 120V, 1440 W, 1.1 m (42") height | 20 kg (45 lb) |
| TOTE422-ADJ/240V | Tote heater with thermostat, 240V, 2880 W, 1.1 m (42") height | 20 kg (45 lb) |
| TOTE481-ADJ/120V | Tote heater with thermostat, 120V, 1440 W, 1.2 m (48") height | 22 kg (50 lb) |
| TOTE482-ADJ/240V | Tote heater with thermostat, 240V, 2880 W, 1.2 m (48") height | 22 kg (50 lb) |
| TOTE-COVER | Tote insulated top cover | |

Comes complete with adjustable and high-limit thermostats for each of 2 heat zones.

Ordering Example: TOTE361-ADJ/120V, tote heater with thermostat, 120V, 1440 W, 0.9 m (36") height, and TOTE-COVER, tote insulated top cover.