PRESSURE RECORDERS

CT87P Series



- 13 mm (0.5") LED Display
- 🛩 152 mm (6") Chart
- ✓ 3 Pressure Ranges
- ✓ 4 Recording Speeds
- Front-Panel Selectable Controls
- Single or Continuous **Chart Rotation**

Free Standing or Wall Mount

The CT87P pressure recorder is a versatile instrument that accurately measures and records pressures. The remote sensor has a 1.8 m (6') long cord and a 17-4 stainless steel pressure port with ¼ NPT threads. The burst pressure is 2500 psi, rated for any gas or fluid compatible with 17-4 stainless steel. Battery backup ensures normal operation during power interruptions. The unit can also be run from any 12 Vdc source (auto or marine).

SPECIFICATIONS

Pressure Ranges psi Model: 0 to 500 psi, 0 to 150 psi, 0 to 50 psi Pressure Ranges bar Model:

0 to 35 bar, 0 to 10 bar, 0 to 3.5 bar Pressure Accuracy: ±1% full scale

Ambient Operating Temp Range: 0 to 60°C (32 to 140°F)

Remote Pressure Sensor: 1.8 m (6') long 17-4 stainless steel ¼ NPT pressure port, 2500 psi burst pressure, rated for any gas or fluid compatible with 17-4 stainless steel

Ambient Operating Relative Humidity: 96% maximum

Selectable Chart Speeds: 6 hours, 24 hours, 7 days, 31 days

Chart Rotation Mode (Selectable): Single turn or continuous

Chart Speed Accuracy: ±1%



Chart Diameter: 152 mm (6") Display: 3-digit, 13 mm (0.5") LED Primary Power Supply: 120 Vac, 50/60 Hz, or 220 to 240 Vac, 50/60 Hz (AC adaptor included)

Battery Life: 48 hours continuous use Battery Backup: 8 "AA" alkaline batteries (included)

Case Size: 235 H x 184 W x 70 mm D (9¼ x 7¼ x 2¾")

Weight:

2.13 kg

(4.7 lb)

Remote sensors included

A

PRESSURE INSTRUMENTS

Case Material: Polycarbonate

To Order		
MODEL NO.	DESCRIPTION	
CT87P	Circular pressure recorder, psi ranges	
СТ87РВ	Circular pressure recorder, bar ranges	
CT87P-230	Circular pressure recorder, psi, 230 Vac	
CT87PB-230	Circular pressure recorder, bar, 230 Vac	
CT87P-RP	Replacement pressure sensor	
CT87-PEN-BLACK	Replacement pen	
CT87P-C-(*)	60 pressure charts	UMEGA
MN1500	"AA" batteries (pack of two)	
(*) Insert pressure range code from chart below.		Extended Warranty Program

PRESSURE	PRESSURE CHART CODES				
RANGE	6 HOURS	24 HOURS	7 DAYS	31 DAYS	
0 to 500 psi	6H500PSI	24H500PSI	7D500PSI	31D500PSI	
0 to 150 psi	6H150PSI	24H150PSI	7D150PSI	31D150PSI	
0 to 50 psi	6H50PSI	24H50PSI	7D50PSI	31D50PSI	
0 to 35 bar	6H35BAR	24H35BAR	7D35BAR	31D35BAR	
0 to 10 bar	6H10BAR	24H10BAR	7D10BAR	31D10BAR	
0 to 3.5 bar	6H3.5BAR	24H3.5BAR	7D3.5BAR	31D3.5BAR	

Comes complete with AC adaptor, 60 assorted charts, 2 pens, 8 "AA" batteries and operator's manual. Ordering Example: CT87P, 152 mm (6") circular pressure recorder with psi ranges, OCW-3, OMEGACARE[™] extends standard 1-year warranty to a total of 4 years.

CT87PB, 152 mm (6") pressure recorder with bar ranges.

OMEGACARE[™] extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.