


STANDARD DIALS—TYPES C AND P


SINGLE SCALE psi-  MOST POPULAR MODELS CHECKED AND HIGHLIGHTED IN RED


Single Scale psi*





 30/0 inHg vac
code: 30V




 0/15 psi
code: 15




 30 inHg vac/0/15 psi
code: 30V/15





 0/30 psi
code: 30




 30 inHg vac/0/30 psi
code: 30V/30





 0/60 psi
code: 60




30 inHg vac/0/60 psi
code: 30V/60




 0/100 psi
code: 100





30 inHg vac/0/100 psi
code: 30V/100




30 inHg vac/0/160 psi
code: 30V/160





 0/160 psi
code: 160




0/200 psi
code: 200




 0/300 psi
code: 300



30 inHg vac/0/300 psi
code: 30V/300



0/400 psi
code: 400




0/600 psi
code: 600


* See pages G-41 through G-44 for PGP and PGC gauge ordering information.

CUSTOM DIAL FACES TYPES C AND P


Special Dials/Dual Scale psi/kg/cm² *




76/0 cmHg
30/0 inHg vac




0/1 kg/cm²
0/15 psi




76 cmHg vac/0/1.0 kg/cm²
30 inHg vac/0/15 psi



0/2 kg/cm²
0/30 psi




76 cmHg vac/0/2.0 kg/cm²
30 inHg vac/0/30 psi




0/4 kg/cm²
0/60 psi




76 cmHg vac/0/4 kg/cm²
30 inHg vac/0/60 psi




0/7 kg/cm²
0/100 psi




76 cmHg vac/0/7 kg/cm²
30 inHg vac/0/100 psi




76 cmHg vac/0/11 kg/cm²
30 inHg vac/0/160 psi




0/11 kg/cm²
0/160 psi




0/14 kg/cm²
0/200 psi




0/21 kg/cm²
0/300 psi



76 cmHg vac/0/21 kg/cm²
30 inHg vac/0/300 psi



0/28 kg/cm²
0/400 psi




0/42 kg/cm²
0/600 psi


* NOTE: To meet the varying needs of our customers, custom dial faces are available; however, they are subject to a \$125 setup fee for Type C and Type P. For each custom dial face, there is a 100-piece minimum for Types C and P.

SPECIAL DIALS TYPES C AND P SINGLE SCALE kPa


Special Dials/Single Scale kPa*




-100/0 kPa




0/100 kPa




-100/150 kPa




0/160 kPa




0/250 kPa




-100/300 kPa




0/400 kPa




-100/500 kPa




0/600 kPa




-100/900 kPa




0/1000 kPa



0/1600 kPa



0/2500 kPa




0/4000 kPa


* NOTE: To meet the varying needs of our customers, custom dial faces are available; however, they are subject to a \$125 setup fee for Type C and Type P. For each custom dial face, there is a 100-piece minimum for Types C and P.

CUSTOM DIAL FACES TYPES C AND P


Special Dials/Dual Scale psi/kPa*




-100/0 kPa
30/0 inHg vac




0/100 kPa
0/15 psi




-100/0/100 kPa
30 inHg vac/0/15 psi




0/200 kPa
0/30 psi




-100/0/200 kPa
30 inHg vac/0/30 psi




0/400 kPa
0/60 psi




-100/0/400 kPa
30 inHg vac/0/60 psi




0/700 kPa
0/100 psi




-100/0/700 kPa
30 inHg vac/0/100 psi




-100/0/1100 kPa
30 inHg vac/0/160 psi




0/1100 kPa
0/160 psi




0/1400 kPa
0/200 psi




0/2000 kPa
0/300 psi



-100/0/2100 kPa
30 inHg vac/0/300 psi



0/2800 kPa
0/400 psi



0/4000 kPa
0/600 psi

* NOTE: To meet the varying needs of our customers, custom dial faces are available; however, they are subject to a \$125 setup fee for Type C and Type P. For each custom dial face, there is a 100-piece minimum for Types C and P.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters