

# LEGAL-FOR-TRADE LOAD CELLS

## NTEP APPROVED PER HB44

### LCCA Series

**Discontinued**

Starts at  
**\$360**

Shown with NTEP approved weigh meter DP41-W, \$595 featured on the following pages



LCCA-1K Shown actual size

**Discontinued**

- ✓ NTEP Approved per HB44
- ✓ Single and Multiple Applications
- ✓ Class III and Class IIIIL Applications

### SPECIFICATIONS

#### NTEP APPROVALS:

LCCA: COC #94-014,



Class III 5,000 division single,

Class IIIIL 10,000 division single

These load cells have Certificate of Conformance (COC) numbers furnished by The National Institute of Standards and Technologies (NIST). NIST uses a National Type Evaluation Program (NTEP) to classify load cells into categories such as class III and IIIIL. HB44 written by NIST gives detailed specifications which the load cells must comply with to be listed as Class III and IIIIL.

Class III is for all commercial weighing unless otherwise specified, and includes chain scales, retail precious metals and semi-precious gem weighing, animal scales and scales used for laundry charges. Class IIIIL is for vehicle, axle-load, livestock, railway track scales, crane and hopper (other than grain hopper) scales.

#### To Order (Specify Model Number)



| MODEL NO.     | PRICE | CAPACITY | LOAD BUTTON  | ROD END       |
|---------------|-------|----------|--------------|---------------|
| LCCA-25-N10K  | \$400 | 25 lb    | LBC-014 \$40 | REC-014M \$15 |
| LCCA-50-N10K  | 400   | 50 lb    | LBC-014 40   | REC-014M 15   |
| LCCA-100-N10K | 415   | 100 lb   | LBC-014 40   | REC-014M 15   |
| LCCA-150-N10K | 415   | 150 lb   | LBC-014 40   | REC-014M 15   |
| LCCA-200-N10K | 415   | 200 lb   | LBC-014 40   | REC-014M 15   |
| LCCA-250-N10K | 415   | 250 lb   | LBC-038 40   | REC-038M 20   |
| LCCA-500-N10K | 415   | 500 lb   | LBC-012 40   | REC-012M 35   |
| LCCA-750-N10K | 415   | 750 lb   | LBC-012 40   | REC-012M 35   |
| LCCA-1K-N10K  | 415   | 1000 lb  | LBC-012 40   | REC-012M 35   |
| LCCA-2K-N10K  | 465   | 2000 lb  | LBC-012 40   | REC-012M 35   |
| LCCA-5K-N10K  | 530   | 5000 lb  | LBC-012 40   | REC-012M 35   |
| LCCA-10K-N10K | 630   | 10000 lb | LBC-034 55   | REC-034M 65   |
| LCCA-15K-N10K | 750   | 15000 lb | LBC-034 55   | REC-034M 65   |
| LCCA-20K-N10K | 1130  | 20000 lb | —            | REC-114M 65   |

Comes with complete operator's manual.

Ordering Example: LCCA-25-N10K is a 25 lb load cell with NTEP approvals, \$400.

Compatible NTEP approved meter for above load cells, DP41-W, \$595.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters