

PORTABLE BENCHTOP METERS

PRECISION 6 DIGIT DISPLAY

**Ω MONOGRAM™
SERIES**

MDS41-E-10V shown smaller than actual size, with PX409, pressure transducer. Visit us online.



MDS41 Series



✓ 5-Year Warranty

OMEGA's DP41 Series meters are available in this attractive, sturdy benchtop case design. The case is 110 H x 260 W x 250 mm D (4.3 x 10.2 x 10") and weighs 2.3 kg (5 lb). Its light weight is ideal for portable operation.

All units feature user-selectable engineering units and come with power cord and operator's manual.

The MDS41 Series meters contain a powerful microprocessor. Features include adjustable filtering, min/max detection, and 6-digit display.

To Order		
STRAIN GAGE MODELS		
MODEL NO.	INPUT	EXCITATION
MDS41-S-50MV	±50 mV	10 Vdc
MDS41-S-100MV	100 mV	10 Vdc
MDS41-W-[*]	Specify	10 Vdc
VOLTAGE/PROCESS MODELS		
MDS41-E-10V	10 Vdc	24 Vdc
MDS25B-E-10V	10 Vdc	24 Vdc
CURRENT PROCESS MODELS		
MDS41-E-MA	4 to 20 mA	24 Vdc

Comes complete with operator's manual.

Ordering Example: MDS41-E-10V, benchtop meter with 10 Vdc range and 24 Vdc sensor excitation.