

- Available from Stock in Convenient 5-Packs
- PFA, Kapton<sup>®</sup>, or Glass Braid Insulation
- ✓ 20, 24, 30, 36 and 40 AWG Wires
- 1 and 2 m (40 and 80") Lengths Standard
- ✓ NIST Calibration Available
- OEM Quantities Available



## Also Available TAP Adhesive Labels

Thermocouple Adhesive Labels secure wire probes to surfaces. **TAP** adhesive labels have a thickness of 0.064 mm (0.0022") and can be used at a maximum temperature of 180°C (356°F). They are made of a polymide film with a silicone pressure sensitive adhesive.

Visit us online for details and ordering information.



Model TAP, roll of 100 adhesive labels, shown smaller than actual size.

Fine 40-Gage PFA Wire Insulation



"GG" Glass braid insulation



To Order			
Model No. ANSI Color Code	AWG Gage	Diameter mm (in)	Insulation
5TC-GG-(*)-20-(**)	20	0.81 (0.032)	Glass Braid
5TC-GG-(*)-24-(**)	24	0.51 (0.020)	Glass Braid
5TC-GG-(*)-30-(**)	30	0.25 (0.010)	Glass Braid
5TC-GG-(*)-36-(**)	36	0.13 (0.005)	Glass Braid
5TC-TT-(*)-20-(**)	20	0.81 (0.032)	PFA
5TC-TT-(*)-24-(**)	24	0.51 (0.020)	PFA
5TC-TT-(*)-30-(**)	30	0.25 (0.010)	PFA
5TC-TT-(*)-36-(**)	36	0.13 (0.005)	PFA
5TC-TT-(*)-40-(**)	40	0.08 (0.003)	PFA
5TC-KK-(*)-20-(**)	20	0.81 (0.032)	Kapton®
5TC-KK-(*)-24-(**)	24	0.51 (0.020)	Kapton®
5TC-KK-(*)-30-(**)	30	0.25 (0.010)	Kapton®

\* Insert calibration **J**, **K**, **T**, or **E**. \*\* Specify length, insert "**36**" for 1 m or "**72**" for 2 m length. **Note:** For GG or TT wire, additional cost per additional 300 mm (12") per package of 5.

For KK wire, additional cost per additional 300 mm (12") per package of 5. For a male straight M8 plug add "M8-S-M" to the model number for additional cost, for a male straight M12 plug add "M12-S-M" to the model number for additional cost. For a male right-angled M8 plug add "M8-R-M" to the model number for additional cost, for a male right-angled M12 plug add "M12-S-M" to the model number for additional cost, for a male right-angled M12 plug add "M12-S-M" to the model number for additional cost. Ordering Example: 5TC-TT-K-30-36, 5 pack, PFA insulated thermocouples, Type K calibration (CHROMEGA®-ALOMEGA®), 30 AWG, 1 m (40") long, stripped lead termination.