

Unique Surface Probes




Adaptor Sold Separately
TAS-K-3
TAS-E-3

All the probes in this series meet the Standard Limits of Error.

**Model No. 88203(*)
Model No. 98203(*)
with Swivel Head**

For rotating, smooth metallic surfaces of 229 to 610 mm (9 to 24") in diameter. 90 m (300') per minute maximum surface velocity. Maximum surface temperature of 205°C (400°F).

Replaceable Element supplied free, for additional elements order Model No. 88203()-RE.*



TAS adaptor
All models supplied with a molded SMP or SMPW subminiature male connector. TAS adaptor sold separately.

A roller-surface probe, for use on moving or rotating, smooth surfaces with a velocity up to 61 m (200') per minute. Maximum surface temperature of 205°C (400°F).

**Model No. 88201(*)
Model No. 98201(*)
with Swivel Head**

Replaceable Element supplied free, for additional elements order Model No. 88201()-RE.*

Visit us online for dimensions.

**Model No. 88202(*)
Model No. 98202(*)
with Swivel Head**


















A roller-surface probe, ideal for measuring outside wall temperatures of smooth plastic or steel piping. Can be used on moving or rotating surfaces of 559 to 1524 mm (22 to 60") in diameter, with 90 m (300') per minute maximum surface velocity. Maximum surface temperature of 205°C (400°F).

Replaceable Element supplied free, for additional elements order Model No. 88202()-RE.*
Ordering Example: 98201K, style 98201 swivel head roller surface probe in Type K thermocouple.

*** Specify Calibration:**
K: CHROMEGA™-ALOMEGA™
E: CHROMEGA™-Constantan




Unique Surface Probes Series 88000




Dimensions: mm (inches)


Unique Surface Probes Series 88000/98000




88108




98201 Swivel
88201




98202 Swivel
88202




98203 Swivel
88203




98220 Swivel
88220




98221 Swivel
88221




88222




88223




88224




98225 Swivel
88225




98226 Swivel
88226




98227 Swivel
88227




88301




88305



88306



88307




88308


Dimensions: mm (inches)

Model 88009

1.5 (0.06) Max. Element Deflection



Model 88014



Model 88013

