

# Temperature/Relative Humidity Chart Recorders



CTH100  
\$300



All Models

- ✓ Continuous Self-Recording
- ✓ Portable, Wall Mount, or Bench Mount
- ✓ 167 mm (6.6") Charts
- ✓ Easily Replaceable Pens
- ✓ 1.5 V Battery Operation Only
- ✓ Models for 1-, 8-, or 32-Day Recording
- ✓ °C or °F

The CTH100 thermo-hygrograph chart recorder measures and records temperature and relative humidity, expensive sensors are unnecessary. This portable, battery operated recorder offers simultaneous recording on its 167 mm (6.6") easy-to-read circular chart. Three recording times are available: 1-day, 8-days, or 32-days. The CTH100's neat appearance and compact size make it ideal for a number of applications in a variety of locations: laboratories, wineries, warehouses, computer rooms, museums, hotels, restaurants, factories, textile mills, paper mills, construction sites, greenhouses, mushroom cultivation farms, and home gardens.

This recorder can be wall or benchtop mounted. Replacement of charts and recording pens is easy. The CTH100 also uses 2 color pens (1 red, 1 blue) to clearly identify the dual trend lines.

## Specifications

**Sensors:** Built-in

**Temperature:** Bimetal

**Humidity:** Nylon film

**Scale Ranges and Operating Environment:**

**Temp:** -10 to 40°C or 10 to 110°F

**Relative Humidity:** 0 to 100% RH (non-corrosive)

**Accuracy:** Temp: ±2°C or ±4°F (minimum scale on chart: 1°C or 2°F)

**Relative Humidity:** ±5% RH between 30 and 90% RH (minimum scale on chart: 2%)

**External Dimensions:**


Approx 200 x 200 x 60 mm (8 x 8 x 2.4")

**Weight:** Approx 650 g (1.5 lb)

**Color of Cover:** Ivory

**Battery/Life:** One 1.5 V, "AA" (included)/1 year

**Pen Life:** 6 months, 1 red and 1 blue (included)



CTH100-1D-F, \$300, shown smaller than actual size.

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)		
Model No.	Price	Ranges
CTH100-1D-F	\$300	10 to 110°F 0 to 100% RH
CTH100-1D-C	300	-10 to 40°C
CTH100-8D-C	300	0 to 100% RH

## Accessories

Model No.	Price	Description
CTH100-C-1D-F	\$14	Chart paper, °F—1 day
CTH100-C-8D-F	14	Chart paper, °F—8 day
CTH100-C-32D-F	14	Chart paper, °F—32 day
CTH100-C-1D-C	14	Chart paper, °C—1 day
CTH100-C-8D-C	14	Chart paper, °C—8 day
CTH100-C-32D-C	14	Chart paper, °C—32 day
CTH100-STAND	35	Stand for CTH100
CTH100-PENSET	25	Replacement pen set, 1 red and 1 blue pen

Comes complete with 1 package of 30 charts, 2 pens, 1 "AA" battery and operator's manual. OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. OMEGACARE<sup>SM</sup> covers parts, labor, and equivalent loaners. Ask your sales representative for full details when placing an order.

**Ordering Examples:** CTH100-1D-F, thermo-hygrograph chart recorder, 1 day, °F, \$300. OCW-3, OMEGACARE<sup>SM</sup> extends standard 1-year warranty to a total of 4 years (\$65), \$300 + 65 = \$365. CTH100-8D-C, -10 to 40°C, 0 to 100% RH, \$300.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters