

# Red Safety Discontinued Product Laboratory Thermometers

GT Series  
Starts at  
**\$25**



See introduction on  
page E-3 to add this option.



- ✓ Safe, Non-Toxic Red Dyed Petrolate
- ✓ May Be Used Where Mercury Is Unusable
- ✓ Graduated to 20°C Minimum to Avoid Column Separation
- ✓ Large Overflow Chamber Protects Against Overheating Damage
- ✓ °F and °C Versions
- ✓ Partial and Total Immersion Styles

## Fahrenheit Models

To Order (Specify Model Number)					
Total Immersion Model No.	Partial Immersion Model No.	Scale Range °F	Div	Length mm (in)	Price
GT-1600RL	—	-330 to 90	2°	356 (14)	\$80
GT-1602RL	GT-3602RL	-150 to 130	2°	305 (12)	65
GT-6450RL	—	-150 to 125	5°	152 (6)	65
GT-1603RL	GT-3603RL	-150 to 220	2°	406 (16)	78
GT-1604RL	GT-3604RL	-60 to 130	2°	305 (12)	40
GT-6455RL	—	-50 to 125	5°	152 (6)	38
GT-1301RL	GT-3301RL	-40 to 125	1°	305 (12)	35
GT-6451RL	—	-40 to 130	2°	152 (6)	25
GT-1302RL	GT-3302RL	0 to 125	1°	305 (12)	30
GT-6452RL	—	30 to 125	1°	152 (6)	25
GT-1317RL	GT-3317RL	-35 to 75	1°	305 (12)	38
GT-1304RL	GT-3304RL	30 to 180	1°	305 (12)	30
GT-6453RL	—	60 to 100	1°	152 (6)	35
GT-1305RL	GT-3305RL	65 to 215	1°	305 (12)	30
GT-6454RL	—	20 to 220	2°	152 (6)	30
GT-1300RL	GT-3300RL	20 to 220	2°	229 (9)	25
GT-1306RL	GT-3306RL	0 to 230	2°	305 (12)	25
GT-1307RL	GT-3307RL	0 to 230	1°	356 (14)	35
GT-1308RL	GT-3308RL	0 to 300	2°	305 (12)	32
GT-1309RL	GT-3309RL	0 to 300	1°	381 (15)	35
GT-1310RL	GT-3310RL	0 to 400	2°	356 (14)	55
GT-1313RL	GT-3313RL	0 to 500	2°	381 (15)	60

Each thermometer comes in a protective plastic shipping tube with operator's manual.

Ordering Examples: **GT-3301RL**, partial immersion style 305 mm (12") thermometer with -40 to 125°F range and 1° division, \$35.



Non-toxic red safety liquid is ideal where mercury is unusable.

   **MOST POPULAR MODELS HIGHLIGHTED!**

## Celsius Models

To Order (Specify Model Number)					
Total Immersion Model No.	Partial Immersion Model No.	Scale Range °C	Div	Length mm (in)	Price
GT-1610RL	—	-200 to 30	1°	356 (14)	\$80
GT-1612RL	GT-3612RL	-100 to 50	1°	305 (12)	65
GT-6401RL	—	-100 to 60	2°	152 (6)	65
GT-1613RL	GT-3613RL	-100 to 100	1°	406 (16)	78
GT-1614RL	GT-3614RL	-50 to 50	1°	305 (12)	40
GT-6400RL	—	-50 to 50	1°	152 (6)	38
GT-1402RL	GT-3402RL	-40 to 50	1°	305 (12)	32
GT-1401RL	GT-3401RL	-40 to 50	½°	305 (12)	38
GT-6404RL	—	-5 to 55	1°	152 (6)	25
GT-6402RL	—	-40 to 50	1°	152 (6)	39
GT-6460RL	—	15 to 40	½°	152 (6)	35
GT-1403RL	GT-3403RL	-15 to 60	1°	254 (10)	32
GT-6410RL	—	-5 to 105	1°	152 (6)	30
GT-1404RL	GT-3404RL	-10 to 110	1°	229 (9)	25
GT-1406RL	GT-3406RL	-20 to 110	1°	305 (12)	25
GT-1407RL	GT-3407RL	-20 to 110	½°	356 (14)	35
GT-1408RL	GT-3408RL	-20 to 150	1°	305 (12)	32
GT-1409RL	GT-3409RL	-20 to 150	½°	381 (15)	38
GT-1410RL	GT-3410RL	-10 to 205	1°	356 (14)	55
GT-1412RL	GT-3412RL	-10 to 260	1°	381 (15)	60

Each thermometer comes in a protective plastic shipping tube with operator's manual.

Ordering Examples: **GT-6460RL**, total immersion style 152 mm (6") thermometer with 15 to 40°C range and ½° division, \$35.



Comes in a variety of lengths and immersion styles.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters