4-Channel Handheld

Data Logger Thermometer

HH374



- Auto Range
- ✓ USB Interface with Windows® Software
- ✓ LED Back Light
- **✓** HOLD Function
- ✓ 4-Channel Input, Type K Thermocouple
- ✓ 4-Channel Display Resolution 0.1°C/0.1°F with Windows® Software
- ✓ MAX/MIN/AVG Function
- Auto Shut-Off for Battery Saving
- ✓ 16,000 Records Data Logger Each Channel
- Certificate of Traceable Calibration Included (No Points)

The HH374 has a high resolution and fast analog to digital converter. Measurements settings and results are shown on the backlit LCD display. Data can be stored in the meter or directly saved on a computer through PC interface. Recorded data can be further processed on a computer. With the exclusive software, recording/recalling of data and programming of logging parameters can be done directly through a PC.

SPECIFICATIONS

Measurement Range: -200 to 1370°C (-328 to 2498°F)

Accuracy: -200 to 1370°C (-328 to 2498°F) $\pm 0.1\%$ rdg + 0.7°C ($\pm 0.1\%$ rdg + 1.4°F)

Input Protection: 60 Vdc or 24 Vrms AC maximum

Battery Type: 9V battery (included)

Operating Condition: 0 to 50°C (32 to 122°F) (<80% RH)

Storage Condition: -20 to 60° C (-4 to 140° F) (<70% RH)

System Required: Windows NT 4.0/NT2000/XP/Vista/

Windows 7

Dimensions: 196 H x 65 W x 36 mm D (7.72 x 2.56 x 1.42")

Approx Weight: 285 g (10.05 oz)



Free Thermocouples Included!

This model includes 4 free 1 m (40") Type K insulated beaded wire thermocouples with subminiature connector (1 per channel).

Order a Spare! Model No. SC-GG-K-30-36



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.



T1

HH374

m

HH374 comes complete with 4 beaded wire Type K thermocouples, 9V battery, hard carrying case, software, USB cable and operator's manual.

HH374

OF OMEGA

T4

тз

THERMOMETER

To Order	
Model No.	Description
HH374	4-channel temperature data logger
HH300-ADAPTER	115 Vac adaptor

Comes complete with 4 beaded wire Type K thermocouples, 9V battery, hard carrying case, software, USB cable and operator's manual.

Ordering Example: HH374, 4-channel thermometer data logger. OCW-3, OMEGACARE™ extends standard 1-year warranty to a total of 4 years.