



Pocket Testers For Temperature and Relative Humidity



Model HH62TH

\$89

Temperature Tester

- ✓ Very Compact and Portable
- ✓ -58 to 302°F (-50 to 150°C) Measuring Range
- ✓ Integral Probe Design
- ✓ °F/°C Switchable

Specifications

Accuracy:
±2°F, 32 to 212°F,
±6°F below 32 and
above 212°F (±1°C,
0 to 100°C, ±3°C below
0 and above 100°C)
Resolution: 1°F/0.1°C
Display: 3½ digit LCD
Battery: 9 V alkaline
Battery Life:
150 hours, alkaline
Dimensions:
5.6 H x 1.8 W x 1.1" D
(142 x 46 x 28 mm)
Weight: 4.6 oz (130 g)

Integral probe allows
one-hand operation



Shown smaller than actual size



Model PTH-1XA

\$49

Temperature and Relative Humidity Tester

- ✓ Simultaneous Display of Temperature and Humidity
- ✓ Auto Power Off (20 min)
- ✓ Memory (Min/Max)
- ✓ °F/°C Switch
- ✓ On/Off Switch
- ✓ Belt or Pocket Clip
- ✓ Batteries Included
- ✓ Pocket Sized
- ✓ Reset Switch
- ✓ Hold Switch

Specifications

Color: Dark Grey
Power Supply: One button cell included (1 CR2032)
Humidity Range: 5 to 95% RH
Accuracy:
10 to 90% RH ±3%
All other ranges ±5%
Temperature:
±14 to 122°F (-10 to 50°C)
Response Time: 80 seconds typical

To Order (Specify Model Number)

Model No.	Price	Description
HH62TH	\$89	Temperature tester
PTH-1XA	49	Temperature and relative humidity tester

Ordering Example: HH62TH, compact temperature tester, \$89



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters