

Economical Video Inspection Systems

HHB200/HHB300



Carrying case included.

- ✓ **HHB200:** 61 mm (2.4") Color LCD Screen for Crystal Clear Image
- ✓ **HHB300:** 88.9 mm (3.5") Color LCD Screen for Superb Clarity and Viewing Effect
- ✓ **12 mm (0.47") Diameter Flexible Camera-Tipped**
- ✓ **View Findings Instantaneously**
- ✓ **Mirror, Magnet and Pick-Up Hook Included**

The HHB200 and HHB300 borescope inspection systems have been designed as a user friendly and economical way of solving hidden problems and increasing productivity. The product has a high clarity color LCD to show clear images. The camera head is housed inside the tip of the probe with adjustable LED lights, which helps you to reach into gaps and holes. The mirror tip is included to make it possible to view different angles. The magnetic tip is used to pick up small metal objects. The hook is used to grab onto objects. The video inspection systems have the advantages of clear images, easy operation and portability. It is widely used in applications such as HVAC/R building, aviation and vehicles maintenance.

Specifications

- Recommended Use:** Indoor
- Viewable Angle:** 60°
- Viewable Distance:** 2.5 to 30 cm (0.98 to 11.8")
- Diameter of Camera Head:** 12 mm (0.47")
- Image Display:**
- HHB200:** 61 mm (2.4") TFT/LCD
 - HHB300:** 88.9 mm (3.5") TFT/LCD

- Resolution:** 320 x 234 pixels
- Probe Length:** 100 cm (39.4")
- Light Source:** Adjustable LED
- Power Source:** 9V alkaline battery (6LR61) included
- Estimated Battery Life:** Approximately 1 hour
- Operating Temperature:** 0 to 45°C (32 to 113°F)
- Operating Humidity:** 5 to 95% RH non-condensing
- Storage Temperature:** -20 to 60°C (-4 to 140°F); 85% (without battery)
- Body Dimensions:**
- HHB200:** 215 H x 156 W x 80 mm D (8.5 x 4.6 x 3.2")
 - HHB300:** 215 H x 156 W x 96 mm D (8.5 x 4.6 x 3.8")
- Weight:** Approximately 0.5 kg (17.6 oz)

HHB200.

To Order	
Model No.	Description
HHB200	61 mm (2.4") color LCD screen borescope
HHB300	88.9 mm (3.5") color LCD screen borescope

Accessories	
Model No.	Description
P230-1	Replacement probe 1 m (3.3') obedient metal
P230-1X	1 m (3.3') obedient probe extension
P230-2X	2 m (6.5') obedient probe extension
P230-3X	3 m (9.8') obedient probe extension

Comes complete with 1 m (3.3') flexible probe, extension tools: (mirror, magnet, pick-up hook), 9V battery, blow mold case, and operator's manual.

Ordering Example: HHB200, 61 mm (2.4") color LCD screen borescope.

