

# Handheld Light Meter

HHLM1337



HHLM1337 shown smaller than actual size.

- 3½-Digit LCD Display LUX, FC,**
- Low-Battery**
- Max/Min Button**
- Data Hold Button**
- Auto Power-Off**
- Easy-to-Use**
- Pocket-Sized and Lightweight**

## Specifications

**Range:** 20/200/2000/20,000 LUX/FC

**Accuracy:** ±3% rdg ±0.5% FS; ±4% rdg ±10 digits for >10,000 LUX/FC

**Resolution:** 0.01 LUX

**Dimensions:**

**Sensor:** 114.3 x 61.0 x 25.4 mm (4.5 x 2.4 x 1")

**Unit:** 188.0 x 63.5 x 25.4 mm (7.4 x 2.5 x 1")

**Power Source:** 6 "AAA" batteries (included)

**Weight:** 5.6 oz (0.5 lb)

The HHLM1337 has a large display for easy viewing of light levels. It can measure a wide range of either LUX or footcandles. Applications include indoor light and work area lighting monitoring and verification useful for facilities engineers, building maintenance personnel and anyone who wants to measure illuminance.

## To Order

Model No.	Description
HHLM1337	Handheld light meter

*Comes complete with operator's manual, light sensor with cover and 6 "AAA" batteries.*

**Ordering Example:** HHLM1337, handheld light meter.