

# OMEGAMETER® Mix and Match Series Digital Multimeters with Non-Contact Voltage Audible Buzzer Feature



HHM33

**Special Non-Contact Voltage Feature:  
Meter Buzzes when Placed Near Live Electrical Circuits.**



HHM34



HHM35

**CHEAPER BY THE DOZEN!  
Purchase any Combination of 12 Units and Save 20%**

All models shown smaller than actual size.



Optional

**3½ digit, 1999 Counts Digital Display**  
**DC Volts:** 0 to 2 V/20 V/600 V ±1.2%  
**AC Volts:** 0-200 V/600 V/50 to 500 Hz ±2.5%  
**DC Current:** 0 to 200 µA/2 mA/20 mA/200 mA/10 A ±2.5%  
**Resistance:** 0 to 200 Ω/2 KΩ/20 KΩ/200 KΩ/20 MΩ ±2.0%  
**Resolution:** 1 mV, 100 mV, 0.1 µA, 0.1 Ω  
**Battery Test:** 1.5 V/9 V ±3.5%  
**Diode Test**  
**10A Fused**  
**Safety Input Jacks**  
**Safety Test Leads**  
**Overload Protection on All Ranges**



Test leads included with all models shown.

**3½ digit, 1999 Counts Digital Display**  
**DC Volts:** 0 to 200 mV/2 V/20 V/600 V ±1.2%  
**AC Volts:** 0 to 200 mV/2 V/200 V/600 V/50 to 500 Hz ±2.0%  
**DC Current:** 0 to 200 µA/20 mA/200 mA/10 A ±1.5%  
**AC Current:** 0 to 200 µA/20 mA/200 mA/10 A/50-500 Hz ±2.0%  
**Resistance:** 0 to 200 Ω/2 KΩ/200 KΩ/20 MΩ ±1.5%  
**Resolution:** 100 µV, 0.1 µA, 0.1 Ω  
**Diode Test**  
**Continuity Test**  
**Non-Contact Voltage Indicator**  
 Low-tension lines from 70 to 440Vac 50 to 60 Hz  
**Data Hold, MAX Hold, 10A Fused, Safety Input Jacks, Safety Test Leads, Overload Protection on All Ranges**

**3200 Counts with Annunciators**  
**Auto Power-Off Function**  
**Auto or Manual Range Selection**  
**Bar Graph Display:** 12 time/sec sampling  
**DC Volts(Auto):** 0 to 320 mV/3.2 V/32 V/320 V/600 V ±1.2%  
**AC Volts(Auto):** 0 to 3.2 V/32 V/320 V/600 V/ 50-200 Hz ±2.0%  
**DC Current:** 0 to 320 µA/3200 µA/32 mA/320 mA/10 A ±2.0%  
**AC Current:** 0 to 320 µA/3200 µA/32 mA/320 mA/10 A ±2.5%  
**Resistance:** 0 to 320 Ω/3.2 KΩ/320 KΩ/3.2 MΩ/30 MΩ ±1.5%  
**Resolution:** 100 µV, 0.1 µA, 0.1 Ω  
**Diode Test**  
**Continuity Test, Data Hold, 10A Fused, Safety Input Jacks, Safety Test Leads, Overload Protection on All Ranges**

## To Order

Model No.	Description
HHM33	Basic DMM
HHM34	Voltage DMM with non-contact feature
HHM35	Multifunction DMM
HHM-TL	Spare set of test leads
HHM-NIST	NIST calibration certificate

Comes complete with test leads and operator's manual.

Ordering Example: HHM35, multifunction DMM and HHM-TL, spare set of test leads.