

Stick Type DMM and DMM/Thermometer

HHM60 Series



- ✓ Highly Accurate Thermometer with Type K Thermocouple (HHM63C/HHM63F/HHM63K)
- ✓ DATA HOLD Function
- ✓ Models with 0.1°, 1° Resolution
- ✓ Auto-Ranging
- ✓ Stick-Type Easy-to-Hold Design
- ✓ Accuracy: Stated Accuracy at 23 ± 5°C <75% RH
- ✓ Battery Life: 200 Hours
- ✓ Dimensions: 170 H x 44 W x 40 mm D (6.7 x 1.8 x 1.6")
- ✓ Weight: Approx. 150 g (5 oz)
- ✓ Valox® Housing to Withstand Accidental Drops
- ✓ CE Marked

Extra Set



HHM60-TL
spare test lead set for HHM60 Series.

Accessories for Stick DMM's and Thermometers

Model No.	Description
MN2400	Extra "AAA" alkaline battery
HHM60-TL	Extra set of test leads
CAL-3-HHM	NIST traceable calibration

HHM64



HHM64
Stick Type Multimeter
3200 count resolution
Analog bargraph function
Backlit LCD display
DCV accuracy: 0.25%

All models shown slightly smaller than actual size.

HHM63



HHM63
Stick Type Multimeter
2500 count resolution
W/Microprocessor-Based DMM
DCV Accuracy: 0.25%
Resistance accuracy: 0.3%
Backlit LCD display
Frequency accuracy up to ± 0.05%
Frequency resolution up to 0.001 Hz

HHM63C/
HHM63F



Comes with beaded Type K thermocouple.

HHM63C/HHM63F
Multimeter Thermometer
2500 count resolution
W/microprocessor-based DMM
DCV accuracy: 0.25%
Resistance accuracy: 0.3%
Backlit LCD display
Frequency accuracy up to ± 0.05%
Frequency resolution up to 0.001 Hz
Type K input
Temp. accuracy ± 2%

Comes complete with soft vinyl carrying case, four "AAA" alkaline batteries, set of safety test leads, Type K beaded wire thermocouple (temperature models only) and operator's manual.

Stick Type Temperature Transducer and Thermometer

Thermocouple Included!

Temperature models include a free 1 m (40") type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy (one per channel).
Order a Spare!
 Model No. SC-GG-K-30-36

Stick Type Temperature Transducer† (no display)

HH63KF-MV
 (°F measurement)
HH63KC-MV
 (°C measurement)



HH63KF-MV/ HH63KC-MV Temperature Transducer

Comes with type K thermocouple, Green LED Power-on, Annunciator, Overload Protection; Accuracy: 0.3% rdg 1 mV/deg analog output for temperature; Connects to any DMM for display

†For Display, Plug Unit into any OMEGA® HHM Series Multimeter. Consult Manual for Instructions.

All Thermocouple Probes Sold Separately See OMEGA's Complete Line of Thermocouple Probes Online.

Stick Type Thermometer HH63K

HH63K Stick Type Thermometer
 3½ digits 2000 counts
 Reading of MAX, DATA HOLD, function overload protection 24 Vac/Vdc
 Accuracy: up to ±0.3%
 °C/°F Switchable
 Comes with beaded type K thermocouple
 0.1/1.0° Resolution

Both models shown smaller than actual size.

To Order

	Model No.	HHM64	HHM63C	HHM63F	HHM63	HH63KF-MV	HH63KC-MV	HH63K
FUNCTIONS	Resolution (counts)	3200	2500	2500	2500	2000	2000	2000
	Range. Auto	•	•	•	•			
	Input Impedance Mohm	>10	>10	>10	>10			
	Analog bargraph	•						
	Analog Output					1 mv/°F	1 mv/°C	
	Range °C		-20~1370				-50~1300°	-50~1300
	Range °F			-4~2498		-58~2372		-58~2000
	Backlit LCD	•	•	•	•			
	Data Hold	•	•	•	•			•
	Capacitance		25 µF	25 µF	25 µF			
	Frequency		5 MHz	5 MHz	5 MHz			
	DCV/ACV-autoranging	600	600	600	600			
	Continuity	•	•	•	•			
Resistance	•	25 MΩ	25 MΩ	25 MΩ				
Diode test	•	•	•	•				
DCV Ω	Basic accuracy, %	0.25	0.25	0.25	0.25			
	Basic accuracy, %	0.3	0.3	0.3	0.3			

All models come complete with soft vinyl carrying case, four "AAA" alkaline batteries, set of safety test leads, Type K beaded wire thermocouple (temperature models only) and operator's manual.

Ordering Example: HH63K, stick thermometer with beaded wire thermocouple.