

Stick-Type Portable MegOhmMeter

HHM65



- ✓ Portable, Simple One Hand Operation
- ✓ Range from 20/2000 MΩ
- ✓ Meter with Backlit LCD Display
- ✓ 3½ Digit 1999 Count Resolution
- ✓ Accuracy: 20 MΩ ± (2% rdg + 2 digits); 2000 MΩ ± (4% rdg + 2 digits); >500 MΩ ± (5% rdg + 2 digits)
- ✓ Provides 500V to Test Insulation
- ✓ Valox® Housing to Withstand Impacts
- ✓ Smallest Insulation Tester
- ✓ External Power Supply Input Jack (6 Vdc)
- ✓ Battery: 4 pcs 1.5V ("AAA" Size) Included (MN2400)
- ✓ Auto Hold, Auto Power-Off
- ✓ Dimensions: 170 H x 43 W x 41 mm D (6.7 x 1.7 x 1.6")
- ✓ Weight: 180 g (6.3 oz)



Test leads included.



HHM65 shown actual size.

To Order	
Model No.	Description
HHM65	MegOhmMeter

Comes complete with soft vinyl carrying case, 4 "AAA" batteries, test leads and operator's manual.

Ordering Example: HHM65, MegOhmMeter.

Accessory

Model No.	Description
MN2400	Spare "AAA" alkaline battery