
○ OMEGA[™] Silicone Rubber **Insulated High Temperature Heater** Hook-Up Wire

HTRG Series



- ✓ 200°C (392°F) **Temperature Rating**
- ✓ UL and CSA Certified*
- ✓ Silicone Rubber Insulated with Treated Glass Overbraid
- ✓ Tinned Copper Conductor

Braided silicone rubber insulated high-temperature lead wires are well suited for use as the exposed leads in appliances and lighting fixtures. HTRG Series wire is also used for range top burners and back panels, steam irons, toasters, broiler ovens, gas dryers, kilns, recessed lighting fixtures and similar applications up to 200°C (392°F).



CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by nonqualified personnel.



To Order						
Gage	Model No.	Туре	Volts	mm (inch)	Nominal OD kg/300 m (lb/1000')	Approx Wt Color
18	HTRG-1CU-618SW-**	7 x 26	600	3.2 (0.13)	5.7 (12.5)	White
18	HTRG-1CU-618SBK-**	7 x 26	600	3.2 (0.13)	5.7 (12.5)	Black
16	HTRG-1CU-616SW-**	7 x 24	600	3.4 (0.13)	7.5 (16.5)	White
16	HTRG-1CU-616SBK-**	7 x 24	600	3.4 (0.13)	7.5 (16.5)	Black
14	HTRG-1CU-614SW-**	7 x 22	600	3.8 (0.15)	10.0 (22.0)	White
14	HTRG-1CU-614SBK-**	7 x 22	600	3.8 (0.15)	10.0 (22.0)	Black
12	HTRG-1CU-612SW-**	19 x 25	600	4.2 (0.17)	14.3 (31.5)	White
12	HTRG-1CU-612SBK-**	19 x 25	600	4.2 (0.17)	14.3 (31.5)	Black
10	HTRG-1CU-610SW-**	19 x 23	600	5.6 (0.22)	23.1 (51.0)	White
10	HTRG-1CU-610SBK-**	19 x 23	600	5.6 (0.22)	23.1 (51.0)	Black

Standard Conductors: AWG 22-20: Nickel Plated Copper or AWG 18-8: Tinned Copper.

Standard Color: White or black. Other colors available; contact Sales.

* *Specify spool length in feet : 25ft (7.6m), 50ft (15.2m), 100ft (30.4m), 250ft (76.2m), 500ft (152m), 1000ft (304m) Ordering Example: HTRG-1CU-616SW-50, a 50' spool of 16 gage stranded wire with white jacketing.

^{*} HTRG Series wire is both UL listed and CSA certified. See heater hook-up wire introduction for current carrying capacity and derating.