

# DC Millivolt Amplifier

## Battery Operated Laboratory Model

OMNI-AMP IIA



- ✓ Heavy-Duty Case
- ✓ Batteries Will Last Over 500 Hours in Continuous Service
- ✓ Specifications and Performance Characteristics The Same as Model OMNI-AMP I



OMNI-AMP IIA shown smaller than actual size.

### To Order

Model No.	Description
OMNI-AMP IIA	DC millivolt amplifier
MN1400-4	Spare 1.5V Type C batteries

Comes complete with operator's manual and (4) 1.5V Type C batteries.  
**Ordering Example:** OMNI-AMP IIA, DC millivolt amplifier.



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.

# Thermocouple DC Millivolt Amplifier

## Battery Operated Laboratory with Built-In ice point™ Reference Junction

OMNI-AMP IIB



- ✓ Heavy-Duty Case
- ✓ Batteries Last Over 500 Hours in Continuous Service
- ✓ Other Specifications and Performance Characteristics the Same as Model OMNI-AMP I
- ✓ Select Calibration K, J, T, E, S, R, C or D
- ✓ Accepts OST Type Male Connectors

**Cold Junction Compensation**



OMNI-AMP IIB shown smaller than actual size.

### To Order

Model No.	Description
OMNI-AMP IIB-(*)	Thermocouple DC millivolt amplifier
MN1400-4	Spare 1.5V Type C batteries
RM12R-B	Spare 3.6V "AA" lithium or equivalent

\* Select thermocouple Type J, K, T, E, R, S, C or D  
 Comes complete with operator's manual, (4) 1.5V Type C batteries, and 3.6V lithium battery.  
**Ordering Example:** OMNI-AMP IIB-K, thermocouple DC amplifier for Type K thermocouple.



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.