Low-Cost Infrared Thermocouple With ABS Plastic Housing


OS36-01 Series All Models





- ✓ 1:1 (60°) Field of View
- ✓ J. K. E. or T **Thermocouple Output Signal**
- Self-Powered
- ✓ No Moving Parts
- ✓ Temperature Compensated
- Measurements to 290°C (550°F)
- High-Strength ABS **Plastic Housing Meets NEMA Ratings**

The OS36-01 Series has revolutionized OMEGA's line of infrared thermocouples. These units feature an exceptionally strong, low-cost hermetically sealed ABS plastic housing. The threaded head can be securely mounted through a bulkhead or threaded into a tapped hole. The OS36-01 Series produce repeatable temperature readings for use in a wide variety of process-monitoring and quality control applications.



styles include the mating connector.

Specifications

Operating Ambient Temperature Range: -18 to 70°C (0 to 160°F)

Field of View: 60° (1:1)


Minimum Spot Size: 8 mm (0.3") Spectral Response: 6.5 to 14 microns

Output Impedance: 3 kΩ Length of Cable: 0.9 m (36") PFA coated unshielded stranded wire

Weight: 40 g (1.4 oz) with cable

Range Chart

Range Code	Temperature Range (2% Accuracy)
50F	-18 to 27°C (0 to 80°F)
80F	10 to 49°C (50 to 120°F)
98.6F	16 to 39°C (60 to 102°F)
140F	25 to 80°C (80 to 180°F)
180F	70 to 104°C (160 to 220°F)
240F	95 to 130°C (200 to 270°F)
280F	125 to 155°C (260 to 310°F)
340F	145 to 175°C (290 to 350°F)
440F	170 to 250°C (340 to 480°F)





OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARES covers parts, labor and equivalent loaners.

To Order Visit omega.com/os36-01 for Pricing and Details		
Model No.	Description	
OS36-01-J-(*)	Type J thermocouple output signal	
OS36-01-K-(*)	Type K thermocouple output signal	
OS36-01-T-(*)	Type T thermocouple output signal	
OS36-01-E-(*)	Type E thermocouple output signal	

^{*} Specify temperature range code from range chart.

Note: Stripped leads are standard.

To order with SMPW subminiature thermocouple connector pair with write-on windows, add suffix "-SMPW" to model number for additional cost.

To order with OSTW standard-size thermocouple connector pair with write-on windows, add

suffix "-OSTW" to model number for additional cost.

Ordering Examples: OS36-01-K-140F-OSTW, thermocouple Type K, 25 to 80°C (80 to 180°F range) with OSTW, standard-size thermocouple connector pair with write-on windows.

OS36-01-J-140F, thermocouple Type J, 25 to 80°C (80 to 180°F) range. **OCW-3**, OMEGACARESM extends standard 2-year warranty to a total of 5 years.