

Reversible Liquid Crystal Temperature Labels


RLC-80 Series

11-Point Temperature Range
 Unique Temperature Bar Design
 Size: 12.7 W x 101.6 L x 0.25 mm Thick (0.5 x 4 x 0.01")

RLC-80-0/100



RLC-80-50/150



RLC-80-100/220



RLC-80-100/220 Series
 Turns Black up to the
 Next Level of Reading.
 Example: 175°F will Start
 to Show Black at 170°F.

Green, Brown, Blue Indicating Systems

All models shown actual size.

BROWN	Bar is just above the actual reading
GREEN	Bar is the actual reading
BLUE	Bar is just below the actual reading

To Order							
Model No.	Temperature Range						
RLC-80-0/100(*)	°F	0	10	20	30	40	
		50	60	70	80	90	100
RLC-80-50/150(*)	°F	50	60	70	80	90	
		100	110	120	130	140	150
RLC-80-100/220(*)	°F	100	110	120	130	140	
		150	160	170	180	200	220

* Insert "-10" for package of 10 or "-30" for package of 30.

Ordering Example: RLC-80-0/100-30, 11-point temperature label (0 to 100°F), package of 30.