

SLIMLINE LAMP WITH ON/OFF SWITCH AND MOTION SENSOR

SL25 Series



- Slim Casing
- Electronic Ballast
- Lamp With or Without Electrical Receptacle
- Magnet Mount (Optional)
- Energy Saving Lamp
- On/Off Switch or Automatic Switching

The flat slimline lamp SL25 with on/off switch or motion sensor is suitable for all types of panels and enclosures, especially where space is at a premium. The lamp can be mounted on its narrow or broad surface using screws. It is also available with a magnet which allows it to be fitted quickly in any position in a steel enclosure. Both versions are available with an integrated electrical receptacle enabling the use of additional appliances. The motion sensor substitutes a door contact switch.

Specifications

Power Consumption: 11 W (equals 75 W light bulb)

Luminosity: 900Lm

Lamp Type: Energy saving lamp, 2G7 base

Service Life: 10,000h

Switch: On/off light switch or PIR movement sensor, approx 6 min fixed switch-on duration

Connection: Terminal 2.5 mm² (0.004 in²) with cable clamp, torque 0.8 Nm max


Mounting: M5 screws (not included) magnet mount (optional)

Casing: Plastic according to UL94 V-0, light gray

Dimensions: 345 x 91 x 40 mm (14 x 3.6 x 1.6")

Weight (Approx): 0.50 kg (18 oz)

Fitting Position: Narrow surface/ broad surface



The Passive Infrared (PIR) motion sensor switches the lighting on when the enclosure door is opened. The switch-on time is reset with every further registered movement. The movement sensor does not react to movement on the other side of glass and so can be used in enclosures with glass doors.



Operating/Storage Temperature:

-20 to 50°C (-4 to 122°F)
-45 to 70°C (-49 to 158°F)

Protection Type: NEMA 4X (IP20)

Approvals: UL File No. E234324

Note: The slimline lamp SL25 is also available with a 483 mm (19") front panel

To Order

Model No.	Protection Type
SL2524001	Light with on/off switch, 11 W, 120 Vac, with receptacle (USA/Canada)
SL2524101	Light with on/off switch, 11 W, 120 Vac, with receptacle (USA/Canada), magnet mount
SL2527010	Light with on/off switch, 11 W, 120 Vac, no receptacle
SL2527110	Light with on/off switch, 11 W, 120 Vac, no receptacle, magnet mount
SL2524004	Light with motion sensor, 11 W, 120 Vac, with receptacle (USA/Canada)
SL2524104	Light with motion sensor, 11 W, 120 Vac, with receptacle (USA/Canada), magnet mount
SL2527012	Light with motion sensor, 11 W, 120 Vac, no receptacle
SL2527112	Light with motion sensor, 11 W, 120 Vac, no receptacle, magnet mount
SL2524005	483 mm (19") light with on/off switch, 11 W, 120 Vac, with receptacle (USA/Canada)
SL2524007	483 mm (19") light with motion sensor, 11 W, 120 Vac, with receptacle (USA/Canada)
SL2527011	483 mm (19") light with on/off switch, 11 W, 120 Vac, no receptacle

Comes complete with operator's manual.

Ordering Examples: SL2524004, light with motion sensor, 11 W, 120 Vac.
SL2524007, light with on/off switch, 11 W, 120 Vac.