
Thermocouple Extension Cables

With Molded Connectors

ANSI color code lEC color code shown

- ✓ Retractable Cable in 1 and 4' Lengths with 5:1 Stretch
- ✓ 24 Gage (0.020" Dia.)
 PFA Coated or Glass
 Overbraid Stranded Wire in
 10 and 25' Lengths
- Molded Quick Disconnect or Subminiature Thermocouple Connectors for Low Cost
- Available in J, K, T and E Calibrations



Model No.	Calibration		Length
TECJ10-(*)	1	Iron- Constantan	3 m (10')
TECJ25-(*)	J		7.5 m (25')
TECK10-(*)	V	CHROMEGA®-	3 m (10')
TECK25-(*)		ALOMEGA®	7.5 m (25')
TECT10-(*)	7	Copper- Constantan	3 m (10')
TECT25-(*)			7.5 m (25')
TECE10-(*)		CHROMEGA- Constantan	3 m (10')
TECE25-(*)			7.5 m (25')

^{*} Insert connector code from chart. Constructed from 24 gage stranded wire.

"N"
Calibration
Available

To order extension cables, specify desired connector combination from chart below

	TOTH CHAIT DCIOW					
Code	Connector #1	Connector #2				
1	OSTW, female	OSTW, female				
2	OSTW, female	OST, male				
3	OSTW, female	SMPW, female				
4	OSTW, female	SMP, male				
5	OST, male	OST, male				
6	OST, male	SMPW, female				
7	OST, male	SMP, male				
8	SMPW, female	SMPW, female				
9	SMPW, female	SMP, male				
10	SMP, male	SMP, male				
11	OSTW, female	Stripped leads				
12	OST, male	Stripped leads				
13	SMPW, female	Stripped leads				
14	SMP, male	Stripped leads				
15	OSTW, female	Spade lug				
16	OST, male	Spade lug				
17	SMPW, female	Spade lug				
18	SMP, male	Spade lug				

Note: OST and OSTW connectors are standard size; SMP and SMPW connectors are subminiature size.

	11111111			
	Glass Braid Wire Extension Cables			Shown smaller than actual size.
	Model No.	(Calibration	Length
•	GECJ10-(*)		Iron-	3 m (10')
r	GECJ25-(*)	J	Constantan	7.5 m (25')
	GECK10-(*)	W/	CHROMEGA-	3 m (10')
	GECK25-(*)	<u> </u>	ALOMEGA	7.5 m (25')
	GECT10-(*)	7	Copper	3 m (10')
	GECT25-(*)		Constantan	7.5 m (25')
	GECE10-(*)		CHROMEGA- Constantan	3 m (10')
	GECE25-(*)			7.5 m (25')

^{*} Insert connector code from chart. Constructed from 24 gage stranded wire.

Shown smaller than actual size.

Retractable Extension Cables

Retractable Extension Cables				
Model No.	Calibration	Length		
RECJ1-(*)	Iron-	30 cm (1')		
RECJ4-(*)	U Constantan	120 cm (4')		
RECK1-(*)	CHROMEGA-	30 cm (1')		
RECK4-(*)	ALOMEGA	120 cm (4')		
RECT1-(*)	Copper-	30 cm (1')		
RECT4-(*)	Constantan	120 cm (4')		
RECE1-(*)	CHROMEGA- Constantan	30 cm (1')		
RECE4-(*)	Constantan	120 cm (4')		

^{*} Insert connector code from chart.

Note: Retractable cables are expandable 5:1, so one foot will expand to 5' in length. **Ordering Example: RECK1-9**, retractable extension cable, SMPW subminiature male or female.