

Pipe Plug Thermistor Probe

ALL MODELS AVAILABLE FOR FAST DELIVERY!

This high-pressure plug sensor is ideal for vessel applications, pressurized containers, and applications requiring NPT mounted security for fixed readings. This accurate thermistor probe is 2252 Ω @ 25°C. Its 304SS sheath has a 6.0 mm (0.25") dia. probe pipe plug, with 2 m (80") of 26 AWG Teflon® insulated stainless steel overbraided stranded wire with stripped leads. Pressure rating is 2500 psi (172 bar). The hex flats are 14.1 mm (0.56") apart, and 16.0 mm (0.63") across points. Hex flats width is 6.0 mm (0.23").



THX-400-NPT-72
\$61
 with Stripped Leads*



Utility Handle Probe THX-400-H Series



Stripped lead termination standard*†

An economical and accurate (2252 Ω @ 25°C) probe with an easy-grip molded handle, 4.5 mm (3/16") dia. and 25.4 mm (1") retractable cable. The 300 mm (12") length probe can be stored in toolboxes or other locations for easy access. The retractable cable expands to 1.5 m (5'); standard termination is stripped lead wires.

THX-400-H
\$91

with Stripped Leads*†

Shown smaller than actual size



T Series Connectors



*Other connector options are available, see Section G. When ordering T Series, please indicate meter to be used.

Phone Plug Connector



† For phone plug termination, add "-PP" to model number and \$7 to price.

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model Number	Price	Length Sheath
THX-400-H-12	\$91	300 mm (12")
THX-400-H-18	94	450 mm (18")
THX-400-H-24	97	600 mm (24")

Accuracy: $\pm 0.2^\circ\text{C}$ from 0 to 75°C, $\pm 1.0^\circ\text{C}$ from -80 to 150°C.

Ordering Example (Stripped Leads): THX-400-H-12, utility handle probe, 12" long with with retractable cable and stripped lead termination, \$91.

Ordering Example (Phone Connector): THX-400-H-12-PP, utility handle probe, 12" long with with retractable cable and phone plug termination, \$98.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters