

Industrial Immersion Heaters for Water, with Thermostat

ARMTIE HEATER



Custom Heaters Available
Contact Sales for Alternative
Length, Thread Size, Sheath
Material, Wattage or
Temperature Range.

- ✓ Incoloy Sheath
- ✓ Incoloy Thermostat Pocket with 5-80°C Rod Thermostat
- ✓ Optional 45-120°C Thermostat
- ✓ IP55 Aluminium Terminal Cover
- ✓ Available for 240 or 415V Operation
- ✓ 21/4" BSP Brass Fitting

To Order (Specify Model Number)

Model No.	Volts	KW	Immersed Length	
			Inch	MM
ARMTIE210	240	2KW	10	254
ARMTIE311	240/415	3KW	11	276
ARMTIE330	240/415	3KW	30	762
ARMTIE411	240/415	4KW	11	276
ARMTIE416	240/415	4KW	16	406
ARMTIE616	240/415	6KW	16	406
ARMTIE630	240/415	6KW	30	762
ARMTIE724	240/415	7.5KW	24	610
ARMTIE927	240/415	9KW	27	686
ARMTIE936	240/415	9KW	36	914
ARMTIE1224	240/415	12KW	24	610
ARMTIE1236	240/415	12KW	36	914
ARMTIE1836	415 delta	18KW	36	914