Data Logger Thermometer

With USB Interface

HH378



HH378 shown smaller than actual size.



- ✓ USB Interface with Windows® Software
- ✓ LED Back Light
- ✓ HOLD Function
- ✓ 4-Channel Input
- J, K, E, T Thermocouple Types
- 4-Channel Display Resolution
- ✓ 0.1°C (0.1°F) with Windows Software
- ✓ MAX/MIN/AVG Function
- ✓ Auto Shut-Off for Battery Saving
- ✓ 16,000 Records per Channel

The HH378 has a high resolution and fast analog-to-digital converter. Measurements settings and results are shown on the backlit LCD display. Data can be stored in the meter or directly saved on a computer through PC interface. Recorded data can be further processed on a computer. With the exclusive software, recording/recalling of data and programming of logging parameters can be done directly through a PC.

Specifications

Measurement Range:

K: -200 to 1372°C (-328 to 2501°F) J: -150 to 1000°C (-238 to 1832°F) E: -150 to 750°C (-238 to 1382°F) T: -180 to 400°C (-292 to 752°F)

Input Protection: 250 Vac

Resolution: 0.1°C/°F <1000, 1°C/°F

≥1000

Accuracy: $\pm (0.1\% \text{ of reading} + 0.7^{\circ}\text{C})$

 \pm (0.1% of reading + 1.4°F) **Below -100°C (-148°F):** \pm (0.4% of reading +0.7°C) \pm (0.4% of reading +1.4°F) **Temperature Coefficient:**

0.01% of reading + 0.05°C per °C (<18°C or >28°C)

Sample Rate: 1 time per second Battery Type: 9V battery (included) Battery Lifetime: Approximately 30 hours (alkaline battery) AC Adapter: 9 Vdc (8 to 10 Vdc

maximum)

Operating Temperature: -10 to 50°C

(14 to 122°F)

Operating Humidity: 10 to 90% RH

(no condensing)

Storage Temperature: -40 to 60°C

(-40 to 140°F)

Storage Humidity: 10 to 75% RH

Dimensions:

196 H x 65 W x 36 mm D (7.72 x 2.56 x 1.42")

Approximate Weight: 310 g (10.93 oz)

System Required: Windows NT 4.0/NT2000/XP/Vista/Windows 7



T1

T3

T4

Free Thermocouples Included!

This model includes 4 free 1 m (40") Type K insulated beaded wire thermocouples with subminiature connector and wire spool caddy (1 per channel).

Order a Spare! Model No. SC-GG-K-30-36

To Order	
Model No.	Description
HH378	4-channel handheld data logger thermometer

Accessories (Field Installable)

Model No.	Description
HH300-ADAPTER	Power adapter (115 Vac)
HH300A-CABLE-USB	Spare USB interface cable

Comes complete with 4 beaded wire Type K thermocouples, 9V battery, hard carrying case, software, USB cable, NIST certificate, and operator's manual.

Ordering Example: HH378, 4-channel data logger thermometer.