




CONSTANT WATTAGE HEATING CABLE ACCESSORIES

For KE and FE Series



Termination Kits for KE Series Model No. Price

Connection/Termination Kits:
 Each connection kit can be used to make one power input splice and two end terminations. Kit contains: one 1" standoff, one panhead screw, two ring terminals, two wire nuts, three lead pouches, two end pouches, one caution label, RTV silicone sealant (3 oz.), and instructions. These assemblies are watertight and suitable for use in Division II locations.

KE-UC-KIT \$39

Connector Kit
 Five end pouches, five lead pouches and a 3 oz. tube of RTV...enough to complete five circuits.

KE-KC-KIT 39

Termination Kits for FE Series Cable

Connection/Termination Kit
 Each connection kit can be used to make one power input connection and two end terminations. Kit contains: one 1" standoff, one panhead screw, two ring terminals, three wire nuts, two barrels, three lead pouches, two end pouches, five shrink tubes, one caution label, RTV silicone sealant (3 oz.) two pipe straps and instructions. These assemblies are watertight and suitable for use in Divisions II locations.

FE-UC-KIT 39

Connection Kit
 Five end pouches, five lead pouches, ten pieces shrink tube...enough to complete five circuits.

FE-KC-KIT 39

Splice Kits

KE Series Cable
 Three lead pouches, three crimp barrels, three terminal lugs (ring type), RTV sealant, one panhead screw, one caution label, one end pouch and instructions.

SK-KIT 21

FE Series Cable
 contains all of the above and also shrink tubing.

FE-SK-KIT 28

Additional Accessories

OMEGALUX™ RTV
 Silicone sealant (3 oz.) used to seal lead and end pouches.

RTV-SS 9

OMEGALUX® Heating Cable Monitor Light Kit:
 Provides a constant continuity check at the end of circuit. For use with all heating cables.

(120V Single Hub)	MLK1-1	91
(240V Single Hub)	MLK2-1	91
(120V Double Hub)	MLK1-2	98
(240V Double Hub)	MLK2-2	98

Junction Box:
 One hub with cover, 1" NPT thread. **JAB-1 29**

Junction Box:
 Two hubs with cover, 1" NPT thread. **JAB-2 34**



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters