

# VACUUM GAUGES ELECTRONIC AND DIGITAL



## DVG-60




- ✓ Reads From 5000 Down to 50 Microns
- ✓ Cleanable Thermistor Sensor for Repeated Accuracy
- ✓ Single Switch Operation
- ✓ Low-Battery Indicator
- ✓ Color-Coded LED Display Shows Vacuum Range
- ✓ Built-In Hanger/Stand
- ✓ Furnished with Vinyl Protective Case

The OMEGA® DVG-60 is a durable, self-contained, battery-powered electronic vacuum gauge that displays the level of vacuum on an LED color-coded readout.

The 10 level color-coded LEDs display the vacuum level from 5000 down to 50 microns.

### SPECIFICATIONS

**Range:** 10 segments to 50 microns  
**Connections:** Standard ¼" male flare fitting  
**Power:** 9V alkaline battery (included)  
**Dimensions:** 140 H x 44.5 W x 38 mm D (5.5 x 1.75 x 1.5")  
**Case:** Polycarbonate  
**Carrying Case:** Included



DVG-60 shown smaller than actual size.

### To Order

MODEL NO.	RANGE
DVG-60	5000 to 50 microns

Comes complete with operator's manual, carrying case, and 9V battery.  
**Ordering Example:** DVG-60, electronic vacuum gauge.

## DVG-64




- ✓ 12,000 to 0 Microns
- ✓ Reads Vacuum in 7 Units of Measure
- ✓ Auto Shut-Off
- ✓ Built-In Hanger
- ✓ Cleanable Sensor

The OMEGA® DVG-64 digital vacuum gauge delivers high precision at a low price. It can accurately read vacuum from 12,000 microns down to 0, over a wide temperature range of 2 to 52°C (35 to 125°F). The vacuum can be displayed in user-selectable units.

### SPECIFICATIONS

**Display:** Updated every ½ second; 1 micron resolution below 200 microns  
**Sensor Type:** Thermistor  
**Connector Type:** Standard ¼" male flare fitting  
**Vacuum Range:** 0 to 12,000 microns (0 to 1600 Pa) with vacuum increasing/decreasing indicator when above 12,000 microns  
**Scale:** Microns, psi, inHg, mbar, Pa, torr, millitorr  
**Operating Temperature Range:** 2 to 52°C (35 to 125°F)  
**Overpressure:** 300 psi max (20 bar)  
**Accuracy:** ±10% (0 to 1000 microns)  
**Power Source:** 9V alkaline battery (included)  
**Continuous Usage:** Over 35 hr  
**Auto Shut-Off:** After 10 minutes when vacuum reading is above 12,000 microns  
**Weight:** 0.2 kg (6.7 oz)  
**Dimensions:** 140 H x 76 W x 32 mm D (5.5 x 3 x 1.25")



DVG-64 shown smaller than actual size.

MODEL NO.	RANGE
DVG-64	12,000 microns to 0

Comes complete with operator's manual and 9V battery.  
**Ordering Example:** DVG-64, digital vacuum gauge.