



pH FIELD & LAB ELECTRODES

pH Buffers and Indicator Papers



Color-Coded Buffer Capsules

For quick preparation of fresh buffer solutions, these color-coded buffer capsules make 100 mL of standard buffer solution accurate to within ± 0.02 pH. Available in three pH ranges,

| To Order | | |
|-----------|--|-------|
| Model No. | Color | Value |
| PHA-94* | Red | pH 4 |
| PHA-97* | Green | pH 7 |
| PHA-100* | Blue | pH 10 |
| Model No. | Description | |
| PHA-4710 | Color-coded buffer sampler 2 capsules each of 4, 7, 10 pH | |

* Each package contains five vials with ten capsules in each.

Buffer Pack

This color-coded buffer pack has two vials, each containing ten capsules of different pH value, four of pH 4.0 (red), four of pH 7.0 (green) and two of pH 10.0 (blue). All values are accurate to within ± 0.02 pH.

| Model No. | Description |
|-----------|--------------|
| PHA-85 | Two vial set |

pH Indicator Paper Dispenser 13 mm (1/2") tape

The dispenser contains one 15 m (50') roll of pH paper and a color comparison chart; measures pH from 0 to 13 in 1 pH unit increments.

| Model No. | Description |
|-----------|--------------------------------------|
| PHA-90 | pH paper dispenser 13 mm (1/2") tape |

Ordering Examples: PHA-94, 5 vials of 10 each red capsules for pH 4 buffer solution.

PHA-90, dispenser 50' of 1/2" pH paper.



Buffers

PHA-100 buffer capsules, pH 10.

PHA-94 buffer capsules, pH 4.

PHA-97 buffer capsules, pH 7.

PHA-90 indicator papers

PHA-85 buffer pack.

Water Quality Test Strips

pH and Total Alkalinity

pH is a natural part of water chemistry. pH Check test strips are designed to offer highly accurate results with minimal cost. For a more comprehensive test try the combination pH/total Alkalinity test strips.

| To Order | | |
|------------|---|--|
| Model No. | Description | Detection Levels PPM (mg/L) |
| WTS-480104 | pH check, 30 pkts of 18 | 2, 3, 4, 5, 6, 6.5, 7, 7.5, 8.5, 9, 9.5, 10, 11, 12 |
| WTS-481104 | pH check, bottle of 50 | pH: 2 to 11 |
| WTS-480005 | pH/total alkalinity, bottle of 50 | pH: 6, 6.5, 7, 7.5, 8.5, 9 TA: 0, 80, 120, 180, 240, 360 PPM |

Ordering Examples: WTS-480104, 30 packets of 18 each pH test strips.
WTS-480005, bottle of 50 pH/total alkalinity test strips.



WTS-480104 water test strips.