

TUBE AND HOSE ACCESSORIES

Tube and Hose Accessories

Hose Cutter

Heavy duty hose cutter for plastic tube and hose up to 1" OD.

Tube Cutter

Make accurate "clean" cuts on tubing from 3 mm ($\frac{1}{8}$ ") to 19 mm ($\frac{3}{4}$ ") OD.

Tubing Marker Clips

Easy-snap clips for marking and identifying tube runs. This complete kit comes in a plastic storage case and includes: 50 each #1 to 9, 50 each of 14 different letters (A, B, C, D, E, F, G, H, J, P, R, X, Y, Z).

Tube Channels

Tube Channel mounts for securing multiple tubing runs. We offer a small and large tube channel. The small 10-Tube Channel is available in 3 sizes to fit tubing OD: 4 ($\frac{5}{32}$ "), 5 ($\frac{3}{16}$ "), 6 ($\frac{1}{4}$ ") [mm (inch)] and can be mounted with self adhesive backing or #4 screw (not included). The large tube channel is available in 6, 7 and 10 channels for tubing sizes 10 mm ($\frac{3}{8}$ ") and 13 mm ($\frac{1}{2}$ ") and can be mounted with two screws (not included).



OHC1, hose cutter.

OTC1-BLK, tubing cutter.



OTMC1-KIT, tube marker kit.

OLTC-12-6, large tube channel.

OSTC-532-10, small tube channel.

To Order

HOSE CUTTER

MODEL NO.	DESCRIPTION
OHC1	Hose cutter, red
OHC1-RE	Replacement blade, single

TUBE CUTTER

OTC1-R	Tubing cutter, red
OTC1-BLK	Tubing cutter, black
OTC1-BL	Tubing cutter, blue
OTC1-RE1	Replacement blade, single
OTC1-RE5	Replacement blades, 5-pack
OTC1-RE10	Replacement blades, 10-pack

TUBE MARKER KIT

OTMC1-KIT	Marker clip kit for 3 mm ($\frac{1}{8}$ ") tubing
OTMC2-KIT	Marker clip kit for 4 mm ($\frac{5}{32}$ ") tubing
OTMC3-KIT	Marker clip kit for 6 mm ($\frac{1}{4}$ ") tubing
OTMC4-KIT	Marker clip kit for 10 mm ($\frac{3}{8}$ ") tubing

TUBE CHANNEL

OLTC-38-7	Large tube channel, 10 mm ($\frac{3}{8}$ ") tubing, 7-channels
OLTC-38-10	Large tube channel, 10 mm ($\frac{3}{8}$ ") tubing, 10-channels
OLTC-12-6	Large tube channel, 13 mm ($\frac{1}{2}$ ") tubing, 6-channels
OSTC-532-10	Small tube channel, 4 mm ($\frac{5}{32}$ ") tubing, 10-channels
OSTC-316-10	Small tube channel, 5 mm ($\frac{3}{16}$ ") tubing, 10-channels
OSTC-14-10	Small tube channel, 6 mm ($\frac{1}{4}$ ") tubing, 10-channels