

Waterproof Digital Thermometer with Probe



DP8891



- ✓ Large LCD
- ✓ High Accuracy Thermistor Probe
- ✓ 0.1 Resolution
- ✓ °C/°F Switchable
- ✓ Battery Powered
- ✓ Waterproof Meter (IP67)
- ✓ Probe Included with Holder


Monitor temperature applications with the DP8891 Series. The DP8891 Series offers a wide temperature range, and can be used both as a portable unit, or a wall mounted large LCD meter. The meter and probe (when connected together) offer waterproof (IP67) rating. Easy to use and °C/°F switchable. Comes complete with probe, probe holder, 4 “AAA” alkaline batteries and wall mount hardware. Replacement probe can be purchased separately.

Specifications

Temperature Range (Thermistor): -10 to 110°C (14 to 230°F)
Temperature Resolution: 0.1°C (0.1°F)
Temperature Accuracy: ±1°C (±1.6°F)
Temperature Response Time: 2 minutes typical
LCD Update Time: 10 seconds
LCD Size: 45 H x 96 mm W (1.77 x 3.78")
Operating Temperature: 0 to 50°C (32 to 122°F)
Operating RH%: Humidity < 80%



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.



DP8891 shown smaller than actual size.

Precision thermistor probe included.

Storage Temperature: -20 to 50°C (-4 to 122°F)
Storage RH%: Humidity < 90%
Dimensions: 122 L x 85 W x 30 mm D (4.80 x 3.35 x 1.18")
Weight: 200 g (7.1 oz)
Battery: 4 alkaline “AAA” (included)
Battery Life: One year (continuously use, alkaline battery)
Probe Size:
Length: 500 mm (20")
Diameter: 5 mm (0.2")
Handle Length: 65 mm (2.6")
Cable Length: 1500 mm (59")
Probe Weight: 80 g (2.8 oz)

Materials:
Meter: ABS
Probe: 304 SS
Connector: Locking mini phone plug
Handle: Nylon (heat resistant to 100°C) silicon
Cable: Nylon (heat resistant to 100°C) silicon (heat resistant to 150°C)

To Order Visit omega.com/dp8891 for Pricing and Details

Model No.	Description
DP8891	Waterproof digital thermometer with probe
DP8891-RP	Replacement thermistor probe

Comes complete with precision thermistor probe, probe holder, 4 “AAA” alkaline batteries, wall mount hardware and operator’s manual.

Ordering Example: DP8891, waterproof digital thermometer with probe and probe holder. **OCW-3**, OMEGACARESM extends standard 1-year warranty to a total of 4 years.