Thermocouple Contacts For Model MTC Connectors **Economical Design HPC Series**

Crimp-Type Attachment Contacts Are Color-Coded Accessories Available

- Hollow Pin Construction

20 to 24 AWG Stranded Wire

OMEGA[®] push-in crimp-style contacts are manufactured from thermocouple alloy materials and are color-coded for easy identification. Contacts are crimp-terminated outside the connector assembly and inserted into the appropriate cavity by means of an insertion tool. They can be readily removed from the connector assembly using a special removal tool. Sealing plugs are available to seal unused positions in lieu of pin or socket.

Important Notes

- 1. MS Standard Assembly Tools are required to crimp and assemble connectors properly. Order with first purchase.
- Match pins and sockets to thermocouple alloys-Example: A 12-cavity connector carries 6 thermocouple circuits (pairs) requiring: 6 positive alloy pins or sockets and 6 negative alloy pins or sockets per body.
- 3. Order bodies in mating pairs. Style MC mates with both style FF and style FC.
- 4. Backshell cable clamps are recommended with each cord style connector.

To Order

Specify Connector Body, Contacts and Backshell (See Note 1).


Example: Cord-to-Cord connectors for 6 type J (Iron-Constantan) thermocouple circuits (pairs).

Male Connector Assembly


- 1. Body: MTC-12-MC
- Pins:
- (+) Pos. Alloy, HPC-IR-P, 1 pkg. (6 required) (-) Neg. Alloy, HPC-CO-P, 1 pkg. (6 required)
- 3. Backshell: MTC-12-SHL

Female Connector Assembly

- 1. Body: MTC-12-FC
- 2. Sockets:
 - (+) Pos. Alloy, HPC-IR-S, 1 pkg. (6 required)
 - (–) Neg. Alloy, **HPC-CO-S**, 1 pkg. (6 required)
- 3. Backshell: MTC-12-SHL



Specially designed MS standard crimping tool MUST be used to crimp wires to pins and sockets properly. Ratchet action ensures a complete crimp every time.



Thermocouple Alloy and Gold-Plated Copper Contacts for Multipin Connectors

To	Order	visit omega.com/hp	c contacts for Pricin	g and Details
----	-------	--------------------	-----------------------	---------------

Alloy Type	Coding Color Letter	Pins (Male)	Sockets (Female)
Iron (+)	BLK M	HPC-IR-P	HPC-IR-S
Constantan (–)	YEL N	HPC-CO-P	HPC-CO-S
Copper (+)	RED C	HPC-CU-P	HPC-CU-S
CHROMEGA [®] (+)	WHT P	HPC-CH-P	HPC-CH-S
ALOMEGA® (–)	GRN R	HPC-AL-P	HPC-AL-S
*Gold-Plated (Uncompensated)	Color Bands [†]	HPC-AU-P	HPC-AU-S

Sealing plugs, model no. **MTC-HP**. * For use with non-thermocouple wire in same body.

Grommets available. Consult Sales Department for price and delivery.

† Pins have red, yellow and brown color bars; sockets have red, blue and black color bars.