


HEAVY DUTY WEIGHING ASSEMBLIES

CAPACITIES TO 150,000 POUNDS



See page F-62 for full details on LCJB Series load cells





See page F-58 for full details on LCTB Series load cells

Complete System From **\$700**

TWA1 ASSEMBLY WITH LCJB LOAD CELL

TWA2 ASSEMBLY WITH LCTB LOAD CELL



MOST POPULAR MODELS HIGHLIGHTED

To Order (Specify TWA Assembly and Load Cell Model Numbers)



TWA ASSEMBLY				MATCHING LOAD CELL		
CAPACITY	MODEL NO.	PRICE	WEIGHT	MODEL NO.	PRICE	WEIGHT
1000 lb	TWA1-4K	\$425	17 lb	LCJB-1K	\$275	2 lb
2500 lb	TWA1-4K	425	17 lb	LCJB-2.5K	275	2 lb
4000 lb	TWA1-4K	425	17 lb	LCJB-4K	275	2 lb
5000 lb	TWA2-20K	315	22 lb	LCTB-5K	625	5 lb
10,000 lb	TWA2-20K	315	22 lb	LCTB-10K	625	5 lb
20,000 lb	TWA2-20K	315	22 lb	LCTB-20K	625	5 lb
30,000 lb	TWA2-50K	835	80 lb	LCTB-30K	715	16 lb
50,000 lb	TWA2-50K	835	80 lb	LCTB-50K	805	16 lb
100,000 lb	TWA2-150K	1150	170 lb	LCTB-100K	1375	24 lb
150,000 lb	TWA2-150K	1150	170 lb	LCTB-150K	1375	24 lb

Ordering Example: To order a system with a maximum capacity of 1,000 lb specify: TWA1-4K, TWA1 Assembly and LCJB-1K, load cell, Price: \$425+ 275= \$700.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters