

# OMEGAMARKER® Temperature Test Kit

- ✓ From 52 to 399°C  
(125 to 750°F) Range
- ✓ 3 Standard Kit Ranges:  
Low, High, Full Range
- ✓ 10 Markers Per Kit
- ✓ Individual Holders for Each Crayon
- ✓ 63 mm (2½") Long Crayons
- ✓ Sharpener and Case  
Included with Kit



OMEGAMARKER  
crayon shown  
actual size.

OMEGAMARKER  
crayon kit  
show smaller than  
actual size.

For added convenience and versatility, OMEGA is introducing the OMEGAMARKER® temperature test kits for those who must measure many different temperatures. Each kit includes 10 individual temperature-sensitive crayons plus a holder for each crayon and a crayon sharpener, all in a self-contained case.

The crayons indicate temperatures from 52 to 399°C (125 to 750°F) and are accurate to within ±1%. Each crayon is 63 mm (2½") long.

The OMEGAMARKER® crayon is easy to use, but certain conditions must be considered. OMEGAMARKERS will not make any mark on smooth or rough surfaces in cold conditions. When rubbed hard on a rough surface, the OMEGAMARKER® gets ground and the powder is deposited on the surface which appears like a mark,

but will not adhere. The correct way of using OMEGAMARKERS would be to strike it across a pre-heated surface during the heating process, using proper safety precautions. While the temperature is below the rated temperature there will not be a visible mark, but as soon as the surface reaches the rated temperature of the marker, at the point of contact the marker will melt and make a visible mark on the surface. This is an indication that the surface has reached the rated temperature of the OMEGAMARKER®.

Typical applications include lab use, forging, heat treating and fabrication of metals, molding of rubber and plastics, and general purpose use on any accessible heated surface.

## Full Range Kit

°F	125	200	250	300	350	425	500	575	650	750
°C	52	93	121	149	177	218	260	302	343	399

There are ten crayons in each kit; one for each temperature (°F/°C).

To Order, Specify:  
**OMEGAMARKER-FULL**

Kit includes  
10 crayons, holders,  
sharpener and case.



## Low Range Kit

°F	125	150	175	200	225	250	275	300	325	350
°C	52	66	79	93	107	121	135	149	163	177

There are ten crayons in each kit; one for each temperature (°F/°C).

To Order, Specify:  
**OMEGAMARKER-LOW**

Kit includes  
10 crayons, holders,  
sharpener and case.

## High Range Kit

°F	300	350	400	450	500	550	600	650	700	750
°C	149	177	204	232	260	288	316	343	371	399

There are ten crayons in each kit; one for each temperature (°F/°C).

To Order, Specify:  
**OMEGAMARKER-HIGH**

Kit includes  
10 crayons, holders,  
sharpener and case.